

16 Way-0° Power Splitter/Combiner

ZC16PD-2185

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)	AMP. UNBAL. (dB)	ISOLATION (dB)		FREQ. (MHz)	VSWR (:1)	
			Adjacent	Opposite		S	OUTPUTS
1800.0	12.55	0.25	21.08	38.52	1880.0	1.02	1.29
1852.0	12.66	0.35	23.33	39.96	1880.0	1.01	1.25
1960.0	12.43	0.23	25.42	40.09	1960.0	1.01	1.23
2040.0	12.46	0.21	29.73	43.64	2040.0	1.01	1.21
2100.0	12.47	0.23	36.51	47.80	2100.0	1.01	1.16
2152.0	12.48	0.25	63.21	53.75	2152.0	1.01	1.10
2184.0	12.48	0.26	41.36	58.87	2184.0	1.01	1.06
2232.0	12.49	0.26	33.74	62.29	2232.0	1.02	1.05
2260.0	12.51	0.26	31.42	56.86	2260.0	1.03	1.08
2300.0	12.53	0.26	29.12	55.06	2300.0	1.04	1.13
2324.0	12.54	0.25	28.10	54.84	2324.0	1.05	1.16
2400.0	12.51	0.23	25.55	49.70	2400.0	1.06	1.19
2480.0	12.48	0.30	23.27	44.76	2480.0	1.08	1.10
2552.0	12.48	0.31	21.19	41.17	2552.0	1.08	1.05
2600.0	12.51	0.35	19.87	39.63	2600.0	1.09	1.20

¹ Total Loss = Insertion Loss+ 12dB Splitter Loss

REV. X2
ZC16PD-2185
100627
Page 1 of 1