

4 Way-0° Power Splitter/Combiner

WP4W1+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
2200	10.20	10.43	10.36	10.13	0.30	6.22	16.64	15.73	16.66	5.23	1.68	1.71	1.71	1.66
2300	9.56	9.76	9.69	9.49	0.27	5.60	17.43	16.42	17.47	4.41	1.65	1.68	1.67	1.63
2400	9.01	9.19	9.12	8.93	0.26	5.08	18.33	17.19	18.41	3.76	1.62	1.63	1.63	1.59
2500	8.54	8.69	8.62	8.46	0.23	4.64	19.37	18.09	19.51	3.22	1.58	1.59	1.59	1.55
2600	8.14	8.26	8.19	8.05	0.21	4.17	20.58	19.14	20.77	2.78	1.55	1.55	1.55	1.52
2700	7.81	7.91	7.84	7.72	0.19	3.76	21.91	20.31	22.22	2.44	1.51	1.50	1.51	1.48
2800	7.56	7.63	7.56	7.46	0.17	3.39	23.37	21.59	23.85	2.18	1.48	1.46	1.46	1.45
2900	7.34	7.39	7.32	7.26	0.14	3.02	25.06	23.08	25.67	1.96	1.45	1.42	1.42	1.42
3000	7.19	7.21	7.14	7.10	0.11	2.63	26.82	24.71	27.57	1.79	1.42	1.39	1.39	1.40
3050	7.12	7.14	7.07	7.04	0.10	2.43	27.72	25.57	28.51	1.72	1.41	1.37	1.37	1.39
3100	7.07	7.08	7.01	6.99	0.09	2.26	28.55	26.44	29.36	1.67	1.41	1.35	1.35	1.38
3150	7.03	7.02	6.95	6.94	0.08	2.12	29.42	27.39	30.05	1.61	1.39	1.34	1.34	1.37
3200	6.99	6.97	6.90	6.90	0.09	1.96	30.16	28.34	30.50	1.57	1.39	1.32	1.32	1.36
3250	6.95	6.93	6.85	6.87	0.10	1.79	30.71	29.20	30.66	1.53	1.37	1.30	1.30	1.36
3300	6.93	6.89	6.82	6.85	0.11	1.60	30.89	29.92	30.56	1.50	1.37	1.29	1.29	1.35
3350	6.91	6.87	6.80	6.83	0.12	1.42	30.69	30.24	30.24	1.49	1.35	1.28	1.28	1.34
3400	6.90	6.85	6.78	6.82	0.13	1.25	30.37	30.31	29.75	1.48	1.35	1.26	1.26	1.34
3450	6.90	6.84	6.76	6.82	0.14	1.08	29.91	30.07	29.18	1.48	1.34	1.26	1.25	1.33
3500	6.90	6.82	6.75	6.82	0.15	0.90	29.42	29.73	28.57	1.48	1.33	1.24	1.24	1.33
3550	6.90	6.82	6.75	6.82	0.15	0.72	28.75	29.07	27.96	1.49	1.33	1.23	1.23	1.32
3600	6.91	6.82	6.75	6.83	0.16	0.59	28.12	28.34	27.37	1.50	1.32	1.23	1.22	1.32
3650	6.92	6.82	6.75	6.84	0.17	0.49	27.44	27.50	26.80	1.53	1.32	1.22	1.22	1.32
3700	6.93	6.83	6.76	6.86	0.18	0.62	26.88	26.81	26.27	1.56	1.32	1.21	1.21	1.31
3750	6.95	6.84	6.77	6.87	0.18	0.75	26.32	26.09	25.76	1.58	1.31	1.20	1.20	1.31
3800	6.97	6.85	6.78	6.89	0.19	0.90	25.83	25.48	25.28	1.61	1.31	1.20	1.20	1.30
3850	6.98	6.86	6.79	6.91	0.20	1.06	25.35	24.92	24.85	1.63	1.30	1.19	1.19	1.30
3900	7.01	6.88	6.81	6.93	0.20	1.22	24.87	24.31	24.43	1.66	1.30	1.19	1.19	1.30
3950	7.03	6.90	6.83	6.95	0.20	1.37	24.43	23.77	24.05	1.69	1.29	1.18	1.18	1.30
4000	7.06	6.92	6.85	6.98	0.21	1.50	23.96	23.23	23.70	1.74	1.30	1.18	1.18	1.30
4050	7.08	6.94	6.87	7.00	0.21	1.65	23.64	22.77	23.36	1.77	1.29	1.18	1.18	1.30
4100	7.12	6.97	6.90	7.03	0.22	1.79	23.27	22.28	23.03	1.81	1.29	1.18	1.18	1.29
4150	7.14	6.99	6.92	7.06	0.22	1.93	22.99	21.88	22.71	1.84	1.28	1.18	1.17	1.29
4200	7.17	7.02	6.95	7.09	0.23	2.07	22.68	21.46	22.43	1.87	1.27	1.17	1.17	1.29
4250	7.21	7.05	6.98	7.12	0.23	2.23	22.42	21.07	22.17	1.91	1.28	1.17	1.17	1.29
4300	7.24	7.08	7.01	7.15	0.23	2.35	22.16	20.69	21.90	1.95	1.26	1.17	1.17	1.29
4400	7.31	7.15	7.07	7.22	0.23	2.61	21.67	19.98	21.42	2.03	1.26	1.17	1.17	1.28
4500	7.37	7.21	7.14	7.29	0.23	2.88	21.31	19.38	21.00	2.11	1.25	1.17	1.17	1.28
4600	7.45	7.29	7.21	7.36	0.24	3.14	20.93	18.79	20.58	2.20	1.24	1.17	1.17	1.27
4800	7.60	7.44	7.36	7.50	0.24	3.69	20.27	17.72	19.90	2.38	1.22	1.18	1.18	1.26
5000	7.75	7.62	7.52	7.64	0.23	4.21	19.63	16.80	19.29	2.58	1.20	1.20	1.20	1.25
5200	7.89	7.78	7.68	7.77	0.21	4.67	19.09	16.03	18.78	2.76	1.19	1.22	1.22	1.24
5400	8.05	7.96	7.86	7.92	0.19	5.23	18.59	15.27	18.33	2.98	1.18	1.24	1.25	1.24
5600	8.18	8.12	8.03	8.05	0.15	5.70	18.22	14.63	17.93	3.17	1.18	1.28	1.29	1.25
5800	8.31	8.28	8.19	8.18	0.13	6.17	17.81	14.00	17.48	3.36	1.18	1.32	1.33	1.25
6000	8.39	8.41	8.32	8.28	0.14	6.79	17.41	13.49	17.02	3.48	1.19	1.37	1.38	1.27
6200	8.48	8.54	8.48	8.40	0.14	7.14	16.94	12.98	16.56	3.61	1.21	1.43	1.44	1.30
6400	8.54	8.66	8.60	8.48	0.18	7.66	16.49	12.60	16.09	3.71	1.24	1.51	1.52	1.34
6600	8.58	8.74	8.71	8.55	0.19	7.93	16.04	12.28	15.59	3.78	1.28	1.58	1.60	1.39
6800	8.62	8.82	8.81	8.61	0.20	8.21	15.54	12.00	15.13	3.80	1.33	1.67	1.69	1.45
7000	8.63	8.87	8.88	8.63	0.25	8.36	15.03	11.70	14.63	3.79	1.37	1.76	1.78	1.50
7200	8.67	8.96	8.96	8.66	0.30	8.35	14.43	11.48	14.09	3.82	1.44	1.88	1.88	1.56
7400	8.69	9.03	9.01	8.66	0.37	8.67	13.93	11.34	13.64	3.80	1.51	1.97	1.97	1.62
7600	8.76	9.14	9.08	8.69	0.45	9.08	13.38	11.14	13.13	3.82	1.59	2.08	2.07	1.67
8000	8.82	9.27	9.07	8.67	0.61	9.59	12.59	11.07	12.35	3.72	1.73	2.27	2.21	1.78

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2

WP4W1+

100627

Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

WP4W1+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10dBm @Temperature = -40°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
2200	10.12	10.35	10.27	10.06	0.29	8.77	16.43	15.52	16.43	5.68	1.67	1.70	1.70	1.66
2300	9.46	9.67	9.59	9.40	0.27	8.21	17.21	16.20	17.23	4.72	1.64	1.67	1.67	1.62
2400	8.92	9.09	9.02	8.83	0.26	7.79	18.10	16.95	18.16	4.01	1.61	1.63	1.63	1.59
2500	8.43	8.58	8.50	8.34	0.24	7.54	19.15	17.87	19.24	3.40	1.58	1.59	1.59	1.56
2600	8.01	8.13	8.05	7.92	0.21	7.18	20.39	18.95	20.49	2.89	1.54	1.54	1.55	1.53
2700	7.69	7.79	7.71	7.60	0.19	6.82	21.66	20.08	21.92	2.54	1.51	1.50	1.52	1.49
2800	7.44	7.51	7.43	7.35	0.17	6.59	23.02	21.28	23.53	2.27	1.47	1.46	1.48	1.46
2900	7.21	7.27	7.19	7.14	0.13	6.31	24.72	22.77	25.34	2.02	1.44	1.42	1.44	1.44
3000	7.05	7.08	7.00	6.97	0.10	5.97	26.42	24.36	27.25	1.84	1.41	1.38	1.39	1.41
3050	6.98	7.00	6.92	6.91	0.10	5.82	27.27	25.16	28.20	1.77	1.40	1.36	1.37	1.39
3100	6.93	6.94	6.85	6.85	0.09	5.69	28.10	26.01	29.07	1.71	1.39	1.34	1.35	1.38
3150	6.87	6.87	6.79	6.80	0.09	5.59	29.08	26.99	29.80	1.64	1.38	1.32	1.33	1.37
3200	6.83	6.81	6.73	6.75	0.10	5.48	29.97	28.04	30.29	1.58	1.37	1.30	1.31	1.36
3250	6.79	6.77	6.68	6.71	0.11	5.35	30.69	29.07	30.50	1.54	1.36	1.28	1.29	1.35
3300	6.77	6.73	6.64	6.68	0.12	5.21	30.90	29.90	30.44	1.50	1.35	1.27	1.28	1.35
3350	6.75	6.71	6.62	6.67	0.13	5.09	30.68	30.26	30.13	1.49	1.34	1.26	1.27	1.34
3400	6.74	6.69	6.60	6.65	0.14	4.97	30.31	30.35	29.65	1.49	1.34	1.24	1.25	1.33
3450	6.74	6.67	6.58	6.65	0.15	4.86	29.83	30.12	29.08	1.49	1.33	1.24	1.24	1.32
3500	6.73	6.66	6.57	6.64	0.16	4.74	29.34	29.78	28.47	1.49	1.32	1.22	1.22	1.31
3550	6.73	6.65	6.56	6.65	0.17	4.63	28.66	29.14	27.86	1.50	1.32	1.22	1.21	1.30
3600	6.74	6.65	6.56	6.65	0.18	4.56	28.03	28.39	27.25	1.51	1.31	1.21	1.20	1.30
3650	6.75	6.66	6.57	6.66	0.19	4.48	27.35	27.51	26.67	1.54	1.31	1.20	1.19	1.30
3700	6.76	6.66	6.57	6.67	0.19	4.39	26.76	26.79	26.13	1.57	1.30	1.19	1.18	1.29
3750	6.78	6.67	6.58	6.69	0.20	4.51	26.16	26.06	25.62	1.60	1.30	1.19	1.18	1.29
3800	6.80	6.69	6.59	6.71	0.20	4.72	25.69	25.41	25.14	1.63	1.30	1.19	1.17	1.29
3850	6.81	6.70	6.61	6.73	0.21	4.92	25.22	24.84	24.69	1.65	1.30	1.18	1.17	1.29
3900	6.84	6.71	6.62	6.75	0.22	5.14	24.78	24.30	24.28	1.68	1.30	1.18	1.17	1.28
3950	6.85	6.73	6.64	6.77	0.22	5.34	24.36	23.78	23.91	1.70	1.29	1.17	1.16	1.29
4000	6.88	6.75	6.66	6.80	0.22	5.52	23.91	23.22	23.55	1.75	1.29	1.17	1.16	1.29
4050	6.91	6.77	6.68	6.82	0.23	5.72	23.54	22.75	23.22	1.78	1.29	1.17	1.16	1.29
4100	6.94	6.80	6.71	6.85	0.23	5.92	23.12	22.21	22.89	1.83	1.28	1.17	1.16	1.28
4150	6.97	6.83	6.74	6.87	0.23	6.11	22.80	21.78	22.57	1.86	1.28	1.17	1.16	1.28
4200	7.00	6.86	6.76	6.90	0.24	6.31	22.50	21.35	22.28	1.90	1.27	1.17	1.16	1.28
4250	7.03	6.88	6.79	6.93	0.24	6.52	22.26	21.01	22.02	1.94	1.27	1.17	1.15	1.27
4300	7.05	6.90	6.81	6.96	0.24	6.69	22.03	20.65	21.76	1.96	1.26	1.17	1.15	1.27
4400	7.12	6.97	6.87	7.03	0.25	7.05	21.51	19.93	21.29	2.05	1.25	1.17	1.15	1.27
4500	7.19	7.04	6.95	7.10	0.25	7.41	21.08	19.28	20.86	2.14	1.25	1.17	1.16	1.27
4600	7.27	7.12	7.02	7.16	0.25	7.78	20.75	18.69	20.45	2.23	1.25	1.17	1.16	1.26
4800	7.40	7.26	7.15	7.30	0.25	8.53	20.12	17.64	19.77	2.40	1.22	1.17	1.18	1.26
5000	7.57	7.44	7.33	7.45	0.24	9.26	19.41	16.66	19.14	2.63	1.20	1.20	1.19	1.25
5200	7.69	7.59	7.47	7.58	0.22	9.92	18.95	15.90	18.63	2.80	1.19	1.23	1.22	1.25
5400	7.85	7.76	7.64	7.71	0.21	10.64	18.42	15.13	18.15	3.04	1.19	1.26	1.24	1.23
5600	7.97	7.92	7.80	7.83	0.17	11.36	18.09	14.53	17.74	3.23	1.19	1.30	1.30	1.26
5800	8.12	8.10	7.99	7.99	0.14	11.97	17.63	13.83	17.29	3.50	1.19	1.34	1.33	1.26
6000	8.13	8.16	8.04	8.02	0.14	12.79	17.37	13.39	16.85	3.52	1.20	1.39	1.39	1.29
6200	8.23	8.30	8.19	8.14	0.16	13.27	16.91	12.85	16.40	3.70	1.22	1.46	1.44	1.31
6400	8.29	8.42	8.31	8.20	0.22	14.13	16.41	12.46	15.94	3.82	1.25	1.54	1.53	1.36
6600	8.37	8.55	8.46	8.31	0.24	14.72	15.90	12.07	15.45	4.01	1.30	1.62	1.62	1.41
6800	8.43	8.65	8.58	8.39	0.26	15.30	15.41	11.78	15.00	4.09	1.35	1.70	1.72	1.47
7000	8.41	8.68	8.62	8.40	0.27	15.80	14.95	11.51	14.54	4.04	1.40	1.81	1.85	1.54
7200	8.45	8.77	8.73	8.46	0.32	15.99	14.32	11.28	14.00	4.12	1.47	1.92	1.97	1.62
7400	8.43	8.79	8.78	8.46	0.35	16.13	13.80	11.09	13.57	4.06	1.54	2.01	2.08	1.68
7600	8.49	8.88	8.85	8.50	0.39	16.25	13.25	10.89	13.05	4.08	1.62	2.11	2.17	1.74
8000	8.54	8.97	8.81	8.59	0.44	17.26	12.50	10.68	12.23	3.94	1.74	2.27	2.28	1.82

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2

WP4W1+

100627

Page 2 of 3

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

WP4W1+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10dBm @Temperature = +85°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
2200	10.26	10.48	10.41	10.19	0.29	7.90	16.75	15.84	16.80	4.98	1.68	1.71	1.70	1.66
2300	9.63	9.82	9.75	9.56	0.26	7.46	17.56	16.53	17.62	4.21	1.65	1.68	1.66	1.63
2400	9.08	9.24	9.17	9.00	0.24	7.05	18.50	17.33	18.58	3.58	1.62	1.64	1.62	1.59
2500	8.60	8.74	8.67	8.52	0.22	6.64	19.58	18.27	19.69	3.08	1.59	1.60	1.58	1.55
2600	8.21	8.32	8.24	8.12	0.19	6.28	20.81	19.34	20.98	2.67	1.55	1.55	1.53	1.51
2700	7.88	7.97	7.89	7.79	0.17	5.94	22.21	20.55	22.45	2.35	1.52	1.50	1.49	1.48
2800	7.63	7.69	7.61	7.54	0.15	5.57	23.74	21.89	24.11	2.10	1.48	1.46	1.45	1.44
2900	7.43	7.46	7.39	7.34	0.12	5.21	25.44	23.41	25.96	1.90	1.45	1.43	1.41	1.42
3000	7.28	7.29	7.22	7.19	0.10	4.94	27.23	25.06	27.91	1.74	1.43	1.39	1.37	1.39
3050	7.22	7.22	7.15	7.13	0.09	4.82	28.15	25.94	28.86	1.68	1.41	1.37	1.36	1.38
3100	7.17	7.16	7.09	7.09	0.08	4.67	28.96	26.84	29.71	1.63	1.41	1.35	1.34	1.37
3150	7.12	7.11	7.03	7.04	0.09	4.65	29.76	27.75	30.38	1.58	1.39	1.34	1.33	1.37
3200	7.09	7.06	6.99	7.01	0.10	4.69	30.39	28.63	30.78	1.54	1.39	1.32	1.31	1.36
3250	7.06	7.02	6.95	6.98	0.11	4.75	30.82	29.40	30.90	1.51	1.37	1.31	1.30	1.35
3300	7.04	6.99	6.92	6.96	0.12	4.84	30.94	30.06	30.74	1.48	1.37	1.29	1.29	1.35
3350	7.03	6.97	6.90	6.95	0.13	4.92	30.71	30.30	30.36	1.47	1.35	1.28	1.28	1.34
3400	7.02	6.95	6.88	6.94	0.14	5.00	30.37	30.30	29.83	1.46	1.35	1.26	1.27	1.34
3450	7.01	6.94	6.87	6.94	0.15	5.06	29.85	29.97	29.23	1.46	1.34	1.26	1.26	1.33
3500	7.01	6.92	6.86	6.94	0.15	5.16	29.32	29.54	28.61	1.46	1.33	1.24	1.25	1.33
3550	7.02	6.92	6.85	6.95	0.16	5.24	28.63	28.88	27.99	1.47	1.33	1.23	1.24	1.33
3600	7.02	6.92	6.86	6.96	0.17	5.40	28.02	28.16	27.39	1.48	1.32	1.23	1.23	1.32
3650	7.04	6.93	6.86	6.97	0.18	5.63	27.37	27.33	26.82	1.51	1.32	1.22	1.22	1.32
3700	7.05	6.93	6.87	6.99	0.18	5.92	26.81	26.65	26.28	1.53	1.31	1.21	1.22	1.32
3750	7.07	6.94	6.88	7.00	0.19	6.19	26.24	25.99	25.78	1.55	1.30	1.20	1.21	1.32
3800	7.09	6.95	6.89	7.02	0.20	6.41	25.75	25.34	25.31	1.58	1.30	1.20	1.21	1.31
3850	7.11	6.97	6.90	7.04	0.20	6.64	25.27	24.76	24.87	1.60	1.29	1.19	1.20	1.31
3900	7.13	6.99	6.92	7.06	0.21	6.83	24.79	24.19	24.46	1.64	1.30	1.19	1.20	1.31
3950	7.15	7.00	6.94	7.09	0.21	7.05	24.37	23.68	24.09	1.66	1.29	1.19	1.19	1.31
4000	7.18	7.03	6.97	7.12	0.22	7.34	23.93	23.12	23.73	1.70	1.29	1.18	1.19	1.31
4050	7.21	7.05	6.99	7.14	0.22	7.57	23.61	22.68	23.39	1.73	1.28	1.18	1.19	1.30
4100	7.24	7.07	7.01	7.17	0.23	7.80	23.24	22.19	23.06	1.77	1.28	1.18	1.18	1.30
4150	7.27	7.10	7.04	7.20	0.23	8.00	22.95	21.78	22.74	1.81	1.27	1.18	1.18	1.30
4200	7.30	7.13	7.07	7.23	0.24	8.19	22.66	21.36	22.46	1.84	1.27	1.17	1.18	1.30
4250	7.34	7.17	7.10	7.27	0.24	8.40	22.39	20.98	22.21	1.89	1.27	1.17	1.18	1.30
4300	7.37	7.20	7.13	7.30	0.24	8.63	22.16	20.62	21.94	1.92	1.26	1.17	1.18	1.30
4400	7.45	7.27	7.20	7.37	0.25	9.12	21.68	19.94	21.46	2.01	1.25	1.17	1.17	1.29
4500	7.52	7.34	7.27	7.44	0.25	9.51	21.32	19.33	21.04	2.09	1.25	1.17	1.17	1.28
4600	7.60	7.42	7.35	7.51	0.25	9.92	20.96	18.74	20.62	2.19	1.24	1.17	1.17	1.27
4800	7.75	7.57	7.49	7.65	0.25	10.81	20.32	17.71	19.96	2.37	1.22	1.18	1.18	1.26
5000	7.89	7.73	7.65	7.79	0.25	11.57	19.72	16.85	19.37	2.56	1.20	1.20	1.19	1.25
5200	8.03	7.89	7.80	7.92	0.23	12.31	19.18	16.07	18.88	2.73	1.18	1.22	1.21	1.24
5400	8.19	8.07	7.97	8.07	0.21	12.95	18.69	15.32	18.44	2.95	1.16	1.24	1.23	1.23
5600	8.32	8.24	8.14	8.21	0.18	13.60	18.32	14.69	18.05	3.14	1.15	1.27	1.27	1.23
5800	8.46	8.41	8.31	8.35	0.15	14.22	17.88	14.06	17.63	3.32	1.15	1.31	1.31	1.24
6000	8.56	8.56	8.46	8.46	0.10	14.71	17.46	13.52	17.17	3.45	1.17	1.35	1.36	1.26
6200	8.66	8.69	8.63	8.60	0.09	15.54	16.99	13.03	16.72	3.58	1.18	1.39	1.42	1.29
6400	8.72	8.80	8.77	8.69	0.11	16.31	16.57	12.68	16.26	3.65	1.20	1.46	1.49	1.33
6600	8.76	8.87	8.89	8.76	0.13	17.29	16.13	12.37	15.76	3.68	1.24	1.53	1.57	1.37
6800	8.78	8.93	8.98	8.80	0.20	18.30	15.66	12.11	15.28	3.65	1.29	1.60	1.66	1.41
7000	8.79	8.99	9.06	8.83	0.27	19.38	15.12	11.83	14.75	3.61	1.33	1.70	1.74	1.46
7200	8.82	9.07	9.12	8.83	0.30	20.52	14.57	11.66	14.19	3.58	1.40	1.82	1.81	1.50
7400	8.85	9.16	9.16	8.82	0.34	21.40	14.07	11.51	13.71	3.55	1.48	1.93	1.89	1.55
7600	8.92	9.29	9.21	8.83	0.46	22.23	13.52	11.43	13.19	3.52	1.56	2.05	1.98	1.61
8000	9.04	9.50	9.24	8.83	0.67	23.01	12.68	11.37	12.42	3.48	1.72	2.27	2.15	1.74

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2

WP4W1+

100627

Page 3 of 3

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see

