

Fixed Attenuator**WR22-ATT-10+***Typical Performance Data (+25°C)*

FREQ.	ATTENUATION	WR22 INPUT VSWR	WR22 OUTPUT VSWR
(GHz)	(dB)	(:1)	(:1)
33.0	10.31	1.05	1.07
33.5	10.30	1.05	1.07
34.0	10.29	1.05	1.06
34.5	10.30	1.05	1.07
35.0	10.36	1.05	1.07
35.5	10.35	1.06	1.07
36.0	10.39	1.05	1.08
36.5	10.41	1.05	1.08
37.0	10.28	1.05	1.08
37.5	10.22	1.05	1.08
38.0	10.32	1.05	1.08
38.5	10.38	1.05	1.08
39.0	10.30	1.05	1.07
39.5	10.31	1.05	1.07
40.0	10.36	1.04	1.07
40.5	10.48	1.04	1.08
41.0	10.42	1.06	1.09
41.5	10.35	1.06	1.08
42.0	10.40	1.06	1.07
42.5	10.58	1.05	1.06
43.0	10.72	1.06	1.06
43.5	10.62	1.05	1.07
44.0	10.49	1.04	1.08
44.5	10.61	1.06	1.08
45.0	10.83	1.06	1.07
45.5	10.94	1.06	1.08
46.0	10.86	1.06	1.08
46.5	10.83	1.06	1.08
47.0	10.92	1.06	1.07
47.5	11.16	1.05	1.07
48.0	11.31	1.05	1.07
48.5	11.28	1.06	1.07
49.0	11.20	1.07	1.08
49.5	11.26	1.06	1.07
50.0	11.44	1.05	1.07



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS