

Fixed Attenuator**WR22-ATT-6+***Typical Performance Data (+25°C)*

FREQ.	ATTENUATION	WR22 INPUT VSWR	WR22 OUTPUT VSWR
(GHz)	(dB)	(:1)	(:1)
33.0	6.67	1.08	1.07
33.5	6.62	1.08	1.10
34.0	6.59	1.06	1.07
34.5	6.58	1.08	1.08
35.0	6.58	1.07	1.07
35.5	6.57	1.05	1.06
36.0	6.53	1.05	1.06
36.5	6.52	1.04	1.07
37.0	6.52	1.06	1.08
37.5	6.53	1.05	1.07
38.0	6.55	1.04	1.07
38.5	6.57	1.05	1.07
39.0	6.58	1.05	1.08
39.5	6.60	1.04	1.08
40.0	6.62	1.05	1.07
40.5	6.64	1.04	1.07
41.0	6.71	1.05	1.07
41.5	6.78	1.06	1.07
42.0	6.83	1.06	1.10
42.5	6.86	1.05	1.08
43.0	6.91	1.07	1.08
43.5	6.96	1.06	1.08
44.0	6.99	1.06	1.07
44.5	7.04	1.07	1.08
45.0	7.08	1.05	1.08
45.5	7.16	1.07	1.10
46.0	7.24	1.08	1.09
46.5	7.29	1.08	1.09
47.0	7.35	1.09	1.10
47.5	7.41	1.08	1.10
48.0	7.47	1.10	1.12
48.5	7.55	1.08	1.11
49.0	7.62	1.10	1.12
49.5	7.67	1.09	1.10
50.0	7.74	1.11	1.11



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS