

**Fixed Attenuator****WR28-ATT-20+***Typical Performance Data (+25°C)*

FREQ.	ATTENUATION	WR28 INPUT VSWR	WR28 OUTPUT VSWR
(GHz)	(dB)	(:1)	(:1)
26.5	18.26	1.10	1.07
27.0	18.42	1.08	1.07
27.5	18.57	1.08	1.08
28.0	18.74	1.10	1.07
28.5	18.94	1.09	1.06
29.0	18.97	1.08	1.05
29.5	19.03	1.07	1.04
30.0	19.27	1.06	1.05
30.5	19.46	1.06	1.06
31.0	19.64	1.06	1.05
31.5	19.82	1.06	1.05
32.0	20.00	1.08	1.05
32.5	20.13	1.07	1.05
33.0	20.11	1.06	1.04
33.5	20.32	1.06	1.04
34.0	20.54	1.05	1.04
34.5	20.76	1.05	1.05
35.0	20.92	1.06	1.05
35.5	21.03	1.05	1.04
36.0	21.10	1.06	1.05
36.5	21.06	1.06	1.05
37.0	21.18	1.05	1.05
37.5	21.44	1.05	1.04
38.0	21.67	1.04	1.03
38.5	21.80	1.05	1.04
39.0	21.90	1.05	1.05
39.5	21.98	1.04	1.04
40.0	22.02	1.06	1.04



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



IF/RF MICROWAVE COMPONENTS

REV. OR  
 WR28-ATT-20+  
 2/18/2026  
 Page 1 of 1