

Fixed Attenuator**WR28-ATT-6+***Typical Performance Data (+25°C)*

FREQ.	ATTENUATION	WR28 INPUT VSWR	WR28 OUTPUT VSWR
(GHz)	(dB)	(:1)	(:1)
26.5	6.24	1.07	1.11
27.0	6.20	1.07	1.10
27.5	6.18	1.08	1.10
28.0	6.20	1.07	1.09
28.5	6.21	1.07	1.08
29.0	6.19	1.08	1.08
29.5	6.18	1.09	1.08
30.0	6.23	1.10	1.08
30.5	6.25	1.08	1.07
31.0	6.29	1.07	1.07
31.5	6.36	1.08	1.06
32.0	6.41	1.08	1.06
32.5	6.44	1.08	1.06
33.0	6.48	1.08	1.06
33.5	6.55	1.10	1.06
34.0	6.60	1.11	1.06
34.5	6.66	1.09	1.05
35.0	6.73	1.07	1.04
35.5	6.80	1.06	1.04
36.0	6.85	1.07	1.05
36.5	6.88	1.08	1.04
37.0	6.95	1.08	1.05
37.5	7.02	1.08	1.06
38.0	7.10	1.08	1.07
38.5	7.17	1.08	1.06
39.0	7.25	1.08	1.05
39.5	7.32	1.08	1.05
40.0	7.39	1.09	1.05



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR
 WR28-ATT-6+
 2/18/2026
 Page 1 of 1