

Typical Performance Data

FREQ.	INSERTION LOSS	INPUT RETURN LOSS	OUTPUT RETURN LOSS
(MHz)	(dB)	(50Ω) (dB)	(75Ω) (dB)
1.00	0.01	13.99	13.98
5.00	0.01	13.97	13.99
10.00	0.01	13.96	14.01
20.00	0.02	13.94	14.04
50.00	0.04	13.89	14.12
100.00	0.08	13.86	14.23
150.00	0.13	13.87	14.31
200.00	0.18	13.91	14.39
250.00	0.23	13.98	14.46
300.00	0.28	14.11	14.55
350.00	0.33	14.30	14.67
400.00	0.36	14.53	14.83
450.00	0.37	14.85	15.07
500.00	0.37	15.28	15.38
550.00	0.35	15.80	15.79
560.00	0.34	15.91	15.88
570.00	0.33	16.02	15.97
580.00	0.33	16.14	16.08
590.00	0.32	16.27	16.19
600.00	0.31	16.40	16.30
650.00	0.26	17.14	16.92
700.00	0.22	18.06	17.69
750.00	0.19	19.15	18.63
800.00	0.17	20.43	19.78
850.00	0.16	22.01	21.16
900.00	0.16	23.88	22.86
950.00	0.16	25.95	24.91
1000.00	0.17	28.48	27.42
1050.00	0.17	31.53	30.50
1100.00	0.18	33.85	34.00
1150.00	0.18	34.37	36.42
1200.00	0.19	33.61	35.94
1250.00	0.20	32.39	34.33
1300.00	0.20	31.58	33.12
1350.00	0.21	31.29	32.46
1400.00	0.21	31.01	32.21
1450.00	0.22	30.38	31.87
1500.00	0.23	29.40	31.06
1550.00	0.24	28.04	29.51
1600.00	0.25	26.41	27.44
1650.00	0.25	24.74	25.47
1700.00	0.25	23.23	23.69
1750.00	0.25	21.95	22.15
1800.00	0.26	20.85	20.90
1850.00	0.26	19.94	19.89
1900.00	0.28	19.30	19.08
1950.00	0.31	18.84	18.50
2000.00	0.35	18.56	18.13
2050.00	0.39	18.50	17.95
2075.00	0.40	18.55	17.93
2100.00	0.42	18.65	17.96
2135.00	0.43	18.86	18.09
2140.00	0.43	18.90	18.11
2145.00	0.43	18.94	18.14
2150.00	0.43	18.98	18.17
2155.00	0.43	19.02	18.20
2160.00	0.43	19.08	18.23
2200.00	0.43	19.54	18.58
2250.00	0.42	20.28	19.21
2300.00	0.40	21.18	20.05