

Typical Performance Data

FREQ.	Insertion Loss	Input Return Loss	Output Return Loss	FREQ.	Group Delay
(MHz)	(dB)	(dB)	(dB)	(MHz)	(ns)
10	74.29	0.09	0.22	9600	0.60
100	81.08	0.20	0.34	9660	0.59
200	76.43	0.27	0.41	9680	0.59
300	72.19	0.31	0.47	9700	0.59
500	67.87	0.37	0.54	9800	0.58
700	65.28	0.41	0.59	9820	0.58
1000	62.20	0.45	0.60	9840	0.58
1500	58.84	0.47	0.55	9860	0.58
2000	56.48	0.47	0.47	9880	0.58
2500	54.72	0.44	0.38	9900	0.58
3000	53.38	0.39	0.32	9920	0.58
3500	52.22	0.34	0.32	9940	0.57
4000	51.30	0.29	0.37	9960	0.57
4500	50.37	0.26	0.45	9980	0.57
5000	49.27	0.25	0.55	10000	0.57
6000	45.75	0.32	0.71	10100	0.57
7000	38.03	0.49	0.79	10120	0.57
7250	35.01	0.54	0.80	10160	0.57
8000	22.25	0.78	0.94	10180	0.57
8240	17.27	0.93	1.10	10200	0.57
9000	2.18	8.62	8.86	10220	0.57
9600	1.39	14.30	14.02	10240	0.57
9700	1.40	14.08	13.75	10260	0.57
9800	1.38	14.68	14.25	10280	0.56
9900	1.33	16.05	15.47	10300	0.56
10000	1.27	18.34	17.52	10360	0.56
10100	1.22	21.44	20.35	10400	0.56
10500	1.27	17.79	18.39	10460	0.55
11000	1.27	21.79	21.54	10500	0.55
11500	1.29	22.28	23.94	10560	0.55
12000	1.35	23.73	31.17	10600	0.54
12500	1.63	13.91	13.85	10660	0.54
13000	1.66	18.95	15.63	10700	0.54
13200	1.70	17.44	15.78	10760	0.54
14000	2.18	15.84	13.80	10800	0.54
14400	3.02	9.83	16.18	10860	0.54
15000	19.41	1.05	2.26	10900	0.54
15400	31.27	0.88	1.85	10960	0.54
15600	35.99	0.88	1.78	11000	0.54
16000	44.06	0.92	1.70	11160	0.54
17000	61.80	0.97	1.68	11180	0.54
17500	70.48	0.96	1.66	11200	0.54
18000	78.26	0.91	1.55	11260	0.54
18200	80.42	0.88	1.49	11280	0.54
18400	78.21	0.85	1.41	11300	0.54
19000	71.07	0.74	1.18	11320	0.54
19200	68.08	0.70	1.11	11340	0.54
19400	65.76	0.67	1.03	11380	0.54
19500	64.45	0.65	0.99	11400	0.54
20000	58.78	0.57	0.82	11500	0.54
20500	55.53	0.54	0.73	11600	0.54
21000	50.57	0.51	0.61	11800	0.54
22000	41.06	0.60	0.50	12000	0.55
22500	36.22	0.73	0.52	12200	0.55
23000	30.96	0.94	0.61	12400	0.55
23500	24.69	1.33	0.84	12600	0.55
24000	16.39	3.08	1.72	12800	0.56
24200	13.95	4.36	2.30	13000	0.59
24700	20.35	1.52	1.13	13100	0.59
25000	28.80	1.50	1.09	13200	0.60