

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	ISOLATION (dB)		Return Loss (dB)	
		RF-DC	RF&DC-DC	RF	RF&DC
360	0.52	58	56	10	10
380	0.43	59	57	11	11
400	0.41	64	57	12	12
420	0.28	62	61	13	13
440	0.23	62	61	14	14
460	0.20	62	62	15	14
480	0.17	63	62	15	15
500	0.14	63	64	17	16
750	0.05	70	71	25	25
1000	0.03	70	72	34	31
1250	0.04	73	73	36	36
1500	0.04	81	81	38	44
1750	0.04	79	89	47	40
2000	0.05	83	80	38	33
2250	0.05	73	73	31	30
2500	0.06	73	74	28	29
2750	0.06	70	70	27	29
3000	0.06	68	67	28	29
3250	0.06	66	63	32	32
3500	0.06	63	63	33	33
3750	0.07	61	61	28	29
4000	0.08	59	60	26	25
4250	0.09	59	59	24	23
4500	0.09	58	58	24	23
4750	0.09	57	57	24	25
5000	0.08	56	56	25	26
5250	0.09	55	55	26	27
5500	0.09	55	55	28	28
5750	0.09	55	55	33	32
6000	0.09	52	54	31	31
6250	0.11	49	49	26	25
6500	0.15	37	36	23	23
6750	0.50	29	27	14	14
7000	0.29	32	31	15	16

