

Coaxial High Pass Filter

ZFHP-2100+

Typical Performance Data

| FREQUENCY (MHz) | INSERTION LOSS (dB) | RETURN LOSS (dB) |
|--------------------|---------------------------|------------------------|
| 10 | 87.84 | 0.01 |
| 50 | 75.72 | 0.03 |
| 100 | 69.65 | 0.04 |
| 200 | 64.50 | 0.05 |
| 400 | 61.46 | 0.07 |
| 900 | 50.86 | 0.09 |
| 1100 | 42.20 | 0.10 |
| 1925 | 30.98 | 0.28 |
| 1950 | 24.73 | 0.33 |
| 2025 | 12.23 | 0.86 |
| 2075 | 5.89 | 2.55 |
| 2100 | 3.49 | 4.71 |
| 2125 | 1.90 | 8.71 |
| 2300 | 0.90 | 10.13 |
| 2500 | 0.45 | 15.64 |
| 3000 | 0.34 | 17.19 |
| 4000 | 0.32 | 24.12 |
| 5000 | 0.35 | 34.09 |
| 6800 | 0.45 | 23.45 |

REV. X1
ZFHP-2100+
081012
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

