

Amplifier

ZFL-2500+

Typical Performance Data

FREQUENCY (MHz)	GAIN (dB)			DIRECTIVITY (dB)			VSWR IN (:1) 5V	VSWR OUT (:1) 5V	NOISE FIGURE (dB) 5V	Pout at 1dB Comp. (dBm) 5V
	4V	5V	6V	4V	5V	6V				
500.0	28.9	30.4	30.59	36.73	42.23	40.95	1.48	1.19	6.08	16.40
625.0	29.8	31.4	31.34	41.02	37.01	49.91	1.58	1.42	6.25	17.22
750.0	29.3	30.7	31.38	45.97	34.04	44.45	1.58	1.59	6.41	17.65
875.0	29.9	31.4	32.68	29.38	30.82	43.66	1.51	1.57	6.59	17.65
1000.0	30.5	32.1	32.93	31.84	28.74	42.15	1.50	1.52	6.84	17.53
1010.0	30.5	32.1	32.83	34.51	31.45	40.63	1.50	1.52	6.89	17.53
1132.5	30.5	32.0	32.47	28.07	34.48	46.73	1.47	1.51	7.25	17.42
1255.0	30.3	31.9	32.49	34.55	40.35	42.13	1.47	1.47	7.68	17.26
1377.5	30.2	31.8	32.47	42.68	36.54	40.51	1.47	1.46	8.12	17.25
1500.0	30.2	32.0	32.34	33.08	30.64	38.03	1.47	1.39	8.45	17.15
1510.0	30.2	32.1	32.26	34.08	30.33	39.34	1.47	1.39	8.43	17.21
1632.5	30.2	32.2	31.83	25.14	31.44	34.32	1.48	1.33	8.59	17.28
1755.0	30.3	32.2	31.62	26.65	27.32	35.09	1.40	1.29	8.56	17.17
1877.5	30.7	32.4	31.56	25.90	23.05	30.59	1.35	1.24	8.47	17.01
2000.0	31.1	32.6	31.53	20.85	22.18	28.08	1.24	1.29	8.36	16.86
2010.0	31.2	32.6	31.52	29.35	22.29	27.47	1.23	1.29	8.37	16.78
2132.0	31.3	32.2	31.38	21.96	22.88	27.51	1.16	1.44	8.22	16.50
2255.0	31.0	31.4	31.32	20.48	21.56	26.74	1.16	1.59	8.11	16.22
2377.0	30.2	30.6	31.15	26.43	24.85	26.58	1.16	1.86	8.09	16.08
2500.0	29.1	29.7	30.29	22.69	27.61	27.12	1.16	2.05	7.97	16.24

REV. X1
ZFL-2500+
060918
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

