

# Frequency Mixer

# ZAD-1+

## Typical Performance Data

RF (MHz)	LO (MHz)	CONVERSION LOSS (dB)			LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
		@LO (dBm)				@LO (dBm)			@LO (dBm)		
		+4	+7	+10		+4	+7	+10	+4	+7	+10
0.5	30.5	7.78	7.29	7.01	0.5	64.00	67.00	64.94	64.00	67.00	56.93
1.0	31.0	7.34	6.89	6.61	1.0	64.00	67.00	63.22	64.00	62.73	56.27
2.0	32.0	6.97	6.49	6.20	2.0	64.00	67.00	61.14	64.00	61.28	55.71
5.0	35.0	6.39	6.01	5.80	5.0	64.00	67.00	60.28	64.00	60.55	55.46
10.0	40.0	6.40	5.99	5.75	10.0	64.00	67.00	59.63	64.00	59.37	55.25
20.0	50.0	6.46	6.02	5.75	20.0	64.00	67.00	58.89	64.00	59.08	55.09
32.7	62.7	6.37	5.96	5.74	32.7	64.00	59.27	56.91	64.00	57.92	54.20
50.0	80.0	6.28	5.91	5.71	50.0	58.05	56.01	54.48	64.00	56.08	53.11
65.0	95.0	6.22	5.87	5.64	65.0	54.46	53.83	52.86	57.32	54.11	51.72
100.0	70.0	6.13	5.81	5.66	100.0	50.35	49.90	48.91	51.33	49.45	47.96
161.6	131.6	6.13	5.84	5.70	161.6	45.29	44.60	44.03	44.16	43.60	43.25
200.0	170.0	6.27	5.99	5.82	200.0	42.19	41.47	41.29	41.32	40.82	40.93
226.1	196.1	6.26	5.95	5.75	226.1	41.04	40.62	40.68	39.98	39.96	40.20
258.3	228.3	6.19	5.89	5.72	258.3	39.93	39.44	39.63	38.30	37.84	38.74
306.7	276.7	6.26	5.99	5.84	306.7	36.83	37.26	37.70	35.84	36.42	36.87
355.0	325.0	6.57	6.23	6.05	355.0	34.24	34.94	35.71	33.81	34.34	35.10
403.3	373.3	6.74	6.32	6.07	403.3	33.60	33.70	34.26	33.74	33.77	34.23
451.7	421.7	7.29	6.68	6.25	451.7	33.90	33.66	34.10	34.38	33.23	33.15
483.9	453.9	7.77	7.17	6.69	483.9	33.99	34.17	34.71	34.99	34.46	34.37
500.0	470.0	7.86	7.25	6.77	500.0	34.23	34.51	35.08	34.62	34.41	34.36

REV. X1  
ZAD-1+  
060615  
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Frequency Mixer

# ZAD-1+

## Typical Performance Data

RF/LO (MHz)	RF VSWR (:1)			LO VSWR (:1)			IF (MHz)	IF VSWR (:1)			LO/RF (MHz)	max. DC output (mV)	DC Offset (mV)
	@LO (dBm)			@LO (dBm)				@LO (dBm)			@LO (dBm)		
	+4	+7	+10	+4	+7	+10		+4	+7	+10	+7		
5.0	1.22	1.21	1.25	1.36	1.98	2.99	5.0	1.47	1.28	1.16	10.0	-270.8	-0.24
17.7	1.12	1.03	1.09	1.29	1.93	2.84	17.7	1.48	1.29	1.17	20.0	-267.8	-0.23
30.4	1.10	1.02	1.09	1.30	1.96	2.82	30.4	1.48	1.30	1.18	24.0	-265.0	-0.21
55.8	1.11	1.06	1.12	1.27	1.86	2.69	55.8	1.50	1.32	1.21	50.0	-261.2	-0.19
81.2	1.12	1.10	1.14	1.25	1.83	2.61	81.2	1.53	1.35	1.25	80.0	-263.8	-0.16
106.5	1.14	1.13	1.17	1.28	1.87	2.68	106.5	1.58	1.40	1.30	100.0	-264.4	-0.15
119.2	1.16	1.15	1.19	1.29	1.88	2.67	119.2	1.60	1.43	1.33	122.0	-267.7	-0.12
144.6	1.19	1.19	1.23	1.31	1.91	2.63	144.6	1.69	1.52	1.42	150.0	-263.5	-0.11
170.0	1.22	1.23	1.26	1.32	1.91	2.59	170.0	1.73	1.54	1.43	178.0	-262.1	-0.07
208.1	1.28	1.29	1.33	1.35	1.92	2.62	208.1	1.86	1.66	1.54	200.0	-261.2	-0.13
233.5	1.33	1.35	1.38	1.39	1.91	2.59	233.5	1.96	1.74	1.62	248.0	-265.8	-0.10
271.5	1.41	1.42	1.46	1.43	1.99	2.65	271.5	2.10	1.88	1.73	276.0	-270.4	-0.18
296.9	1.47	1.49	1.52	1.48	1.99	2.63	296.9	2.18	1.97	1.80	304.0	-266.9	-0.26
322.3	1.53	1.56	1.58	1.52	1.99	2.66	322.3	2.29	2.07	1.90	332.0	-250.0	-0.23
360.4	1.62	1.65	1.68	1.62	2.03	2.64	360.4	2.45	2.19	2.03	360.0	-231.2	-0.47
398.5	1.73	1.74	1.77	1.73	2.16	2.72	398.5	2.59	2.33	2.13	388.0	-211.9	-0.18
423.8	1.80	1.81	1.83	1.77	2.20	2.83	423.8	2.65	2.40	2.20	430.0	-189.5	-0.45
461.9	1.92	1.93	1.94	1.80	2.27	2.90	461.9	2.76	2.49	2.29	458.0	-184.4	-0.03
487.3	1.99	2.00	2.00	1.82	2.25	2.87	487.3	2.81	2.53	2.32	486.0	-184.5	-0.13
500.0	2.03	2.03	2.02	1.83	2.26	2.86	500.0	2.79	2.55	2.33	500.0	-181.3	-0.33

REV. X1  
ZAD-1+  
060615  
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

