

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
2000	0.18	27.42	20.50	22.73	23.08	22.61
2100	0.19	27.12	21.05	22.08	22.50	21.55
2200	0.20	26.85	21.64	21.60	21.89	20.82
2300	0.20	26.58	22.36	21.11	21.22	20.37
2400	0.21	26.34	23.07	20.60	20.49	20.27
2500	0.22	26.10	23.96	19.97	19.79	20.36
2600	0.23	25.87	24.58	19.29	19.00	20.64
2750	0.25	25.57	25.95	18.56	18.32	21.61
3000	0.28	25.09	26.62	17.69	17.65	22.87
3250	0.28	24.67	23.60	17.37	17.11	21.62
3500	0.29	24.35	20.14	17.33	17.06	19.52
3750	0.30	24.10	17.81	17.59	17.24	19.20
4000	0.29	23.90	15.99	18.17	17.80	22.65
4500	0.28	23.62	13.83	20.41	20.67	22.28
4750	0.27	23.61	12.99	21.74	21.85	17.50
5000	0.28	23.78	12.17	23.17	23.00	16.57
5250	0.26	24.00	11.90	25.53	26.57	17.97
5500	0.25	24.28	11.96	32.48	35.10	22.94
5600	0.24	24.40	12.05	34.25	37.03	28.03
5700	0.24	24.54	12.13	30.81	32.27	30.94
5800	0.24	24.73	12.33	28.31	28.74	24.44
5900	0.24	24.99	12.90	26.18	26.08	19.92
6000	0.25	25.45	14.63	23.71	23.58	18.07
6400	0.31	25.17	10.14	17.92	18.34	10.73
6600	0.36	25.64	11.09	16.59	16.71	10.94
6800	0.37	26.09	11.86	16.50	16.91	11.17
7000	0.37	26.77	12.65	17.36	18.57	10.16