

Coaxial Band Pass Filter

ZFBP-EDU2180

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.30	31.80	0.01	5	204.60
0.35	30.49	0.01	10	30.24
1.30	20.78	0.05	15	14.40
3.90	20.58	0.50	20	11.09
4.00	23.81	0.61	22	10.47
4.55	3.25	7.23	24	10.06
4.60	2.49	9.23	26	9.79
5.00	0.74	24.72	28	9.61
25.00	0.19	29.73	30	9.52
38.00	0.21	30.14	32	9.48
70.00	0.84	22.12	34	9.50
74.20	2.74	9.59	36	9.57
74.50	3.21	8.19	38	9.67
78.70	20.57	1.15	40	9.82
79.90	30.97	0.88	42	10.00
80.00	32.11	0.87	44	10.23
89.00	31.66	0.42	46	10.51
200.00	42.24	0.40	48	10.86
350.00	59.52	4.54	50	11.27
500.00	73.04	0.70	55	12.72
850.00	60.66	1.10	60	15.19
1500.00	59.29	9.04	62	16.67
1750.00	58.44	6.60	65	19.80
2000.00	42.65	6.85	70	29.99