

Coaxial High Pass Filter

ZFHP-0R055-S+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.009	80.97	0.02
0.012	86.90	0.04
0.015	85.48	0.06
0.020	88.75	0.09
0.040	73.86	0.63
0.042	60.68	1.84
0.043	54.10	2.45
0.044	47.51	3.06
0.045	40.92	3.67
0.046	34.33	4.28
0.048	21.16	5.50
0.049	14.57	6.11
0.050	7.99	6.71
0.052	6.68	12.61
0.055	4.73	21.44
0.057	3.42	27.34
0.058	2.77	30.28
0.060	1.47	36.17
0.065	1.17	32.03
0.070	0.87	27.88
0.080	0.66	19.72
0.100	0.43	20.57
0.200	0.17	22.29
0.500	0.08	23.96
0.800	0.05	27.30
1.000	0.04	29.01
1.500	0.03	32.18
2.000	0.03	34.35
5.000	0.02	40.45
10.000	0.02	42.91
20.000	0.04	43.59
50.000	0.05	38.95
100.000	0.07	31.40
120.000	0.12	28.42
140.000	0.18	28.82
160.000	0.32	25.54
180.000	0.55	26.35
200.000	0.20	39.60
250.000	0.18	30.19
300.000	0.33	28.61
350.000	0.21	29.52
400.000	0.20	26.26
500.000	0.46	22.67
600.000	0.74	21.72
700.000	0.48	26.45
800.000	0.65	22.25
900.000	0.61	22.23
1000.000	0.96	24.10

REV.OR
ZFHP-0R055-S+
200225
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

