

# Coaxial High Pass Filter

# ZFHP-2100-S+

## Typical Performance Data

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | RETURN<br>LOSS<br>(dB) |
|--------------------|---------------------------|------------------------|
| 10                 | 87.84                     | 0.01                   |
| 50                 | 75.72                     | 0.03                   |
| 100                | 69.65                     | 0.04                   |
| 200                | 64.50                     | 0.05                   |
| 400                | 61.46                     | 0.07                   |
| 900                | 50.86                     | 0.09                   |
| 1100               | 42.20                     | 0.10                   |
| 1925               | 30.98                     | 0.28                   |
| 1950               | 24.73                     | 0.33                   |
| 2025               | 12.23                     | 0.86                   |
| 2075               | 5.89                      | 2.55                   |
| 2100               | 3.49                      | 4.71                   |
| 2125               | 1.90                      | 8.71                   |
| 2300               | 0.90                      | 10.13                  |
| 2500               | 0.45                      | 15.64                  |
| 3000               | 0.34                      | 17.19                  |
| 4000               | 0.32                      | 24.12                  |
| 5000               | 0.35                      | 34.09                  |
| 6800               | 0.45                      | 23.45                  |

REV. OR  
ZFHP-2100-S+  
200526  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

