

High Pass Filter

ZX75HP-EDU2567+

Typical Performance Data

Connected

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	(nsec)
0.30	74.24	0.04	150.0	12.45
1.00	64.23	0.03	180.0	4.63
9.00	45.32	0.00	190.0	3.74
29.00	36.75	0.01	205.0	2.91
59.00	38.99	0.04	350.0	0.89
75.00	61.92	0.07	370.0	0.82
101.00	36.73	0.21	450.0	0.62
121.00	35.97	0.57	490.0	0.56
125.00	39.57	0.79	550.0	0.49
126.00	39.23	0.87	700.0	0.41
128.00	28.85	1.09	850.0	0.36
130.00	20.47	1.47	890.0	0.35
136.00	4.79	7.67	920.0	0.35
138.00	2.76	15.15	950.0	0.34
150.00	0.84	20.62	970.0	0.33
500.00	0.16	28.79	995.0	0.34
850.00	0.18	30.23	1000.0	0.33
1000.00	0.19	29.51	1080.0	0.33
1800.00	0.30	19.49	1140.0	0.32
2250.00	0.39	16.22	1190.0	0.32
2750.00	0.47	14.83	1220.0	0.32
2950.00	0.50	14.77	1800.0	0.29



P.O. Box 350166, Brooklyn, New York 11235-0003 • (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
ZX75HP-EDU2567+
URJ
170619
Page 1 of 1