

High Pass Filter

ZX75HP-EDU2573+

Typical Performance Data

Connected

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10	78.91	0.01	3000	2.24
100	56.98	0.01	3250	75.00
250	49.01	0.00	3500	0.73
500	43.19	0.01	3750	0.56
1600	38.09	0.12	4000	0.47
2000	45.33	0.18	4250	0.43
2500	41.82	0.34	4500	0.40
2800	43.13	0.60	4750	0.38
2926	30.38	0.95	5000	0.37
2966	19.91	1.28	5250	0.35
3000	12.81	1.98	5500	0.34
3086	3.09	8.94	5750	0.33
3116	2.31	11.00	6000	0.32
3200	1.50	13.46	6250	0.32
4000	0.78	12.53	6500	0.32
5000	0.50	17.22	6750	0.32
5500	0.58	14.89	7000	0.32
6000	0.72	13.01	7250	0.32
6500	0.67	15.08	7350	0.32
7000	0.58	18.94	7500	0.31
8000	1.44	9.13	7900	0.30
9000	1.02	12.85	8000	0.30



P.O. Box 350166, Brooklyn, New York 11235-0003 • (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
ZX75HP-EDU2573+
URJ
170619
Page 1 of 1