



THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|------------|-------------|--------|-----|------|
| OR | ECO-007104 | NEW RELEASE | MAR 21 | DDR | VC |
| | | | | | |
| | | | | | |

**SUGGESTED MOUNTING CONFIGURATION
FOR UC2731 CASE STYLE**



NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS $.010 \pm .0010$. COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

| UNLESS OTHERWISE SPECIFIED | INITIALS | DATE |
|----------------------------|--------------|-----------|
| DIMENSIONS ARE IN INCHES | DRAWN: DDR | 29 MAR 21 |
| TOLERANCES ON: | CHECKED: RR | 29 MAR 21 |
| 2 PL DECIMALS ± | APPROVED: NN | 29 MAR 21 |
| 3 PL DECIMALS ± .005 | | |
| ANGLES ± | | |
| FRACTIONS ± | | |

Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL DWG, UC2731 C.S, 50 OHM, ABF

Mini-Circuits®
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

| | | | |
|---------------|-------------------|-----------------------|---------|
| SIZE: A | CODE IDENT: 15542 | DRAWING NO: 98-PL-652 | REV: OR |
| FILE: 98PL652 | SCALE: 10:1 | SHEET: 1 OF 1 | |