

Adapter

Mini-Circuits

50 DC to 50 GHz 2.4 mm-Female to 2.4 mm-Female

THE BIG DEAL

- Ultra-Wideband, DC-50 GHz
- Flat Response
- Low Insertion Loss, 0.11 dB
- Excellent VSWR, 1.04:1



24FPM-24F+

Generic photo used for illustration purposes only

Model No. 24FPM-24F+			
Case Style	DJ3008		
Connectors	2.4 mm-F to 2.4 mm-F		

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

KA/KU band

APPLICATIONS5G mmW,

Satellite Communications

PRODUCT OVERVIEW

Mini-Circuits' 24FPM-24F+ is a wideband bulkhead adapter supporting a wide range of applications from DC to 50 GHz. This model provides excellent VSWR, low insertion loss, and flat response versus frequency. The 24FPM-24F+ features passivated stainless steel construction and measures only 0.77" in length.

KEY FEATURES

Features	Advantages		
Wideband, DC to 50 GHz	Wide frequency range provides application flexibility and makes this model ideal for broadband and multi-band use.		
Excellent VSWR, 1.04:1	Provides good matching for 50Ω systems and minimizes signal reflections across wide frequency range.		
Low insertion loss, 0.11 dB	Provides excellent signal power transmission from input to output.		
Passivated stainless steel construction	Stands up to wear and tear in demanding environments and provides excellent reliability.		
Very wide operating temperature range, -55 to +100 °C	Withstands extreme operating conditions and is suitable for use near high power componentry where heat rise is common		



BULKHEAD Adapter

24FPM-24F+

Mini-Circuits

50Ω

DC to 50 GHz 2.4 mm-Female to 2.4 mm-Female

ELECTRICAL SPECIFICATIONS AT 25°C						
Parameter	Condition (GHz)	Min.	Тур.	Max.	Units	
Frequency Range	—	DC	—	50	GHz	
	DC-10	_	0.05	0.2		
	10-20	_	0.08	0.2	dB	
Insertion Loss	20-40	_	0.11	0.2		
	40-50	_	0.13	0.25		
VSWR	DC-10	_	1.01	1.2		
	10-20	_	1.01	1.2	:1	
	20-40	_	1.04	1.2		
	40-50	_	1.04	1.2		

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings		
Operating Temperature	-55°C to +100°C		
Storage Temperature	-55°C to +100°C		

Permanent damage may occur if any of these limits are exceeded.

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com PAGE 2 OF 4



Adapter

Mini-Circuits

DC to 50 GHz 2.4 mm-Female to 2.4 mm-Female


24FPM-24F+

COAXIAL CONNECTIONS

50Ω

Connector 1	2.4 mm-F		
Connector 2	2.4 mm-F		

OUTLINE DRAWING



OUTLINE DIMENSIONS (Inches)

А	В	С	D	Е	wt
0.362	0.276		0.720		grams
9.20	7.00		18.30		5.0



BULKHEAD Adapter


24FPM-24F+


Mini-Circuits

50Ω

DC to 50 GHz 2.4 mm-Female to 2.4 mm-Female

TYPICAL PERFORMANCE DATA AND CHARTS				
Frequency	Insertion Loss (dB)	VSWR (:1)		
(MHz)		2.4 mm-Female	2.4 mm-Male	
10	0.01	1.02	1.02	
100	0.01	1.00	1.00	
500	0.02	1.01	1.01	
2000	0.03	1.01	1.01	
4000	0.05	1.02	1.02	
6000	0.06	1.01	1.01	
10000	0.06	1.01	1.01	
15000	0.07	1.01	1.02	
20000	0.09	1.03	1.04	
25000	0.10	1.06	1.06	
30000	0.10	1.01	1.02	
35000	0.11	1.04	1.04	
40000	0.11	1.01	1.03	
46000	0.12	1.09	1.09	
50000	0.16	1.09	1.09	





NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights C. and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Mini-Circuits