



Mini-Circuits

COAXIAL

# Adapter

24FR-KM+

50Ω DC to 40 GHz Right-Angle 2.4 mm-Female to 2.92 mm-Male

## KEY FEATURES

- Ultra-Wideband, DC to 40 GHz
- Low Insertion Loss, 0.13 dB Typ.
- Excellent VSWR, 1.10:1 Typ.
- Right-Angle Body



Generic photo used for illustration purposes only

## PRODUCT OVERVIEW

Mini-Circuits' 24FR-KM+ is a coaxial 2.4 mm Right-Angle Female to 2.92 mm Male adapter supporting a wide range of applications from DC to 40 GHz. This model provides excellent VSWR and low insertion loss versus frequency. The 24FR-KM+ features passivated stainless-steel construction and measures only 0.755" in length.

## ELECTRICAL SPECIFICATIONS<sup>1</sup> AT +25°C

Parameter	Frequency (GHz)	Min.	Typ.	Max.	Units
Frequency Range		DC		40	GHz
Insertion Loss	0.01-40	—	0.13	0.47	dB
VSWR	0.01-40	—	1.10	1.38	:1

1. Specifications are tested to minimum frequency of 0.01 GHz.

## ABSOLUTE MAXIMUM RATINGS<sup>2</sup>

Operating Case Temperature	-45 °C to +125 °C
Storage Temperature	-45 °C to +125 °C

2. Permanent damage may occur if any of these limits are exceeded.








COAXIAL

# Adapter

**24FR-KM+**

50 $\Omega$  DC to 40 GHz Right-Angle 2.4 mm-Female to 2.92 mm-Male

## TYPICAL PERFORMANCE GRAPHS





COAXIAL

# Adapter

**24FR-KM+**


Mini-Circuits

50Ω DC to 40 GHz Right-Angle 2.4 mm-Female to 2.92 mm-Male

## CONNECTOR SPECIFICATIONS

Description	Connector 1	Connector 2
Connector Type	2.4 mm-Female	2.92 mm-Male
Orientation	Right-Angle	Straight

## CASE STYLE DRAWING



Weight: 8.2 grams

Dimensions are in mm [inches]. Tolerances: 2 PL± 0.40 mm

## PRODUCT MARKING\*: 24FR-KM+

\*Marking may contain other features or characters for internal lot control.





Mini-Circuits

COAXIAL

# Adapter

24FR-KM+

50Ω DC to 40 GHz Right-Angle 2.4 mm-Female to 2.92 mm-Male

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DJ3787-2
RoHS Status	Compliant
Environmental Ratings	ENV152

## NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)

