

Engineering Development Model

Power Splitter/Combiner 3ZB2CS-ED12265/2

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-1174

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		1750		2220 MHz
Isolation	1750 - 2220 MHz		25	dB
Insertion Loss Above 3.0 dB	1750 - 2220 MHz		0.35	dB
Phase Unbalance	1750 - 2220 MHz		0.335	deg.
Amplitude Unbalance	1750 - 2220 MHz		0.019	dB
VSWR	SUM Port		1.20	(:1)
	OUT Ports		1.15	(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

Functional Diagram

