

Frequency Mixer

ADE-ED11949/1

Level 7 (LO Power + 7 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD542

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	900		2440	MHz
	RF (f _L to f _U)	900		2440	MHz
	IF	10		1500	MHz
Conversion Loss	Total Range		6.7		dB
LO-RF Isolation			31		dB
LO-IF Isolation			28		dB
Input IP3			+12.5		dBm
1 dB Compression			+2		dBm

MAXIMUM RATINGS	
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
LO	6
RF	4
IF	3
GROUND	1,2,5

Electrical Schematics

