

# Low Noise Amplifier

# ZX60-3011+

## Typical Performance Data

FREQUENCY (MHz)	GAIN (dB) 15V	DIRECTIVITY (dB) 15V	VSWR IN (:1) 15V	VSWR OUT (:1) 15V	NOISE FIGURE (dB) 15V	Pout at 1dB Comp. (dBm) 15V	FREQUENCY (MHz)	Output IP3 (dBm) 15V
400.0	16.13	8.71	1.81	1.72	1.25	21.41	400.0	30.78
500.0	15.92	8.87	1.77	1.70	1.28	21.36	500.0	30.98
600.0	15.74	9.10	1.74	1.69	1.37	21.54	900.0	31.16
700.0	15.52	9.44	1.72	1.68	1.48	21.46	1000.0	31.31
800.0	15.29	9.74	1.70	1.68	1.65	21.42	1200.0	31.44
900.0	14.96	10.15	1.69	1.67	1.73	21.53	1400.0	31.52
1000.0	14.78	10.28	1.67	1.66	1.75	21.48	1600.0	31.58
1100.0	14.57	10.58	1.67	1.65	1.67	21.50	1800.0	31.74
1200.0	14.13	10.86	1.67	1.65	1.59	21.47	1900.0	31.70
1300.0	13.97	11.13	1.67	1.63	1.48	21.45	2100.0	31.82
1400.0	13.68	11.46	1.67	1.62	1.40	21.30	2300.0	31.81
1500.0	13.25	11.56	1.67	1.61	1.42	21.27	2400.0	31.69
1600.0	13.08	11.68	1.68	1.59	1.41	21.32	2600.0	31.77
1700.0	12.76	11.82	1.69	1.58	1.46	21.36	2900.0	31.82
1800.0	12.46	11.86	1.71	1.58	1.55	21.31	3000.0	31.74
1900.0	12.27	11.84	1.72	1.58	1.66	21.19		
2000.0	12.01	12.05	1.73	1.57	1.71	21.05		
2100.0	11.80	12.11	1.73	1.58	1.75	20.94		
2200.0	11.57	12.03	1.73	1.59	1.72	20.79		
2300.0	11.12	12.44	1.74	1.60	1.78	20.73		
2400.0	10.81	12.00	1.74	1.62	1.71	20.61		
2500.0	10.73	12.06	1.75	1.65	1.67	20.37		
2600.0	10.13	12.45	1.74	1.67	1.65	20.38		
2700.0	9.98	11.74	1.73	1.69	1.66	20.33		
2800.0	10.13	11.71	1.71	1.73	1.75	19.84		
2900.0	9.57	12.12	1.69	1.76	1.83	19.80		
3000.0	9.46	11.56	1.70	1.80	1.95	19.75		

REV. X1  
 ZX60-3011+  
 070515  
 Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

