

Frequency Mixer

ADE-ED14942/1

Level 17 (LO Power + 17 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.

At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD541

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _u)	20		750	MHz
	RF (f _L to f _u)	20		750	MHz
	IF	DC		250	MHz
Conversion Loss	mid band		6.5		dB
	Total Range		6.8		dB
LO-RF Isolation	Low Range		43		dB
	Mid Range		40		dB
	Upper Range		38		dB
LO-IF Isolation	Low Range		42		dB
	Mid Range		40		dB
	Upper Range		36		dB
Input IP3			+26		dBm
1 dB Compression			+9		dBm

Note: Low Range = [f_L to 10f_L]
mid band = [2f_L to f_u/2]

Mid Range = [10f_L to f_u/2]

Upper Range = [f_u/2 to f_u]

MAXIMUM RATINGS	
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
LO	6
RF	4
IF	3
GROUND	1,2,5

