

Frequency Mixer

ADE-ED6545/1

Level 7 (LO Power + 7 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD542

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fu)	10		1000	MHz
	RF (fL to fu)	10		1000	MHz
	IF	10		600	MHz
Conversion Loss	mid band		5.6		dB
	Total Range		6.2		dB
LO-RF Isolation	Low Range		69		dB
	Mid Range		50		dB
	Upper Range		35		dB
LO-IF Isolation	Low Range		50		dB
	Mid Range		38		dB
	Upper Range		26		dB
Input IP3			+16		dBm
1 dB Compression			+1		dBm

Note: Low Range = [fL to 10fL]
mid band = [2fL to fu/2]

Mid Range = [10fL to fu/2]

Upper Range = [fu/2 to fu]

MAXIMUM RATINGS	
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
LO	6
RF	2
IF	3
GROUND	1,4,5

Electrical Schematic

