

## Frequency Mixer

## ADE-ED6913/1

Level 3 (LO Power +3 dBm)

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

**CASE STYLE : CD542**

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	110		1103	MHz
	RF (fL to fU)	110		1103	MHz
	IF	0		600	MHz
Conversion Loss	mid band		6.4		dB
	Total Range		6.7		dB
LO-RF Isolation	Low Range		41		dB
	Mid Range		-		dB
	Upper Range		35		dB
LO-IF Isolation	Low Range		40		dB
	Mid Range		-		dB
	Upper Range		31		dB

**Note:** Low Range = [fL to 10fL]      Mid Range = [10fL to fU/2]      Upper Range = [fU/2 to fU]  
mid band = [2fL to fU/2]

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	6
RF	4
IF	3
GROUND	1, 2, 5