

Frequency Mixer

ADE-ED7014/1

Level 10 (LO Power +10 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD542

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	5		1300	MHz
	RF (fL to fU)	5		1300	MHz
	IF	0		1000	MHz
Conversion Loss	mid band		6.6		dB
	Total Range		6.5		dB
LO-RF Isolation	Low Range		63		dB
	Mid Range		45		dB
	Upper Range		31		dB
LO-IF Isolation	Low Range		66		dB
	Mid Range		43		dB
	Upper Range		26		dB

Note: Low Range = [fL to 10fL] Mid Range = [10fL to fU/2] Upper Range = [fU/2 to fU]
mid band = [2fL to fU/2]

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	6
RF	3
IF	2
GROUND	1, 4, 5