

Frequency Mixer

ADE-ED7383/3

Level 7 (LO Power +7 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD542

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	0.1		332	MHz
	RF (fL to fU)	0.1		332	MHz
	IF	0.1		290	MHz
Conversion Loss	mid band		4.7		dB
	Total Range		5.3		dB
LO-RF Isolation	Low Range		-		dB
	Mid Range		51		dB
	Upper Range		37		dB
LO-IF Isolation	Low Range		-		dB
	Mid Range		46		dB
	Upper Range		30		dB

Note: Low Range = [fL to 10fL] Mid Range = [10fL to fU/2] Upper Range = [fU/2 to fU]
mid band = [2fL to fU/2]

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	6
RF	3
IF	2
GROUND	1, 4, 5