

## Frequency Mixer

## ADE-ED7941/1

Level 7 (LO Power + 7 dBm)

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

**CASE STYLE : CD542**

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fu)	10		1990	MHz
	RF (fL to fu)	10		1990	MHz
	IF	10		1000	MHz
Conversion Loss	Mid Range		7.2		dB
	Total Range		7.7		dB
LO-RF Isolation	Low Range		50		dB
	Mid Range		41		dB
	Upper Range		29		dB
LO-IF Isolation	Low Range		53		dB
	Mid Range		39		dB
	Upper Range		34		dB
Input IP3			+12		dBm
1 dB Compression			+1		dBm

**Note:** Low Range = [fL to 10fL]

Mid Range = [10fL to fu/2]

Upper Range = [fu/2 to fu]

Mid band = [2fL to fu/2]

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
LO	6
RF	2
IF	3
GROUND	1,4,5

### Electrical Schematics

