

Engineering Development Model

Power Splitter/Combiner ADP-ED10239/1

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD636

ELECTRICAL SPECIFICATIONS 75Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		5		1000	MHz
Isolation	5-50 MHz		36		dB
	50-500 MHz		35		dB
	500-1000 MHz		23		dB
Insertion Loss Above 3.0 dB	5-50 MHz		0.35		dB
	50-500 MHz		0.45		dB
	500-1000 MHz		0.75		dB
Phase Unbalance	5-50 MHz		0.030		deg.
	50-500 MHz		0.276		deg.
	500-1000 MHz		0.458		deg.
Amplitude Unbalance	5-50 MHz		0.005		dB
	50-500 MHz		0.007		dB
	500-1000 MHz		0.033		dB
VSWR	SUM Port		1.07		(:1)
	OUT Ports		1.09		(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	1
PORT 1	3
PORT 2	4
GROUND	6
NOT USED	2,5

Functional Diagram



Mini-Circuits®

ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350188, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4851 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINICIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. X2
ADP-ED10239/1
12/15/2008
Page 1 of 1