

## Power Splitter/Combiner

## ADP-ED10239/2

### 2 Way-0°

#### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD636

ELECTRICAL SPECIFICATIONS 75Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		5		1000 MHz
Isolation	5 - 50 MHz		35	dB
	50 - 500 MHz		32	dB
	500 - 1000 MHz		22	dB
Insertion Loss Above 3.0 dB	5 - 50 MHz		0.35	dB
	50 - 500 MHz		0.50	dB
	500 - 1000 MHz		0.80	dB
Phase Unbalance	5 - 50 MHz		0.020	deg.
	50 - 500 MHz		0.044	deg.
	500 - 1000 MHz		0.122	deg.
Amplitude Unbalance	5 - 50 MHz		0.003	dB
	50 - 500 MHz		0.003	dB
	500 - 1000 MHz		0.021	dB
VSWR	SUM Port		1.15	(:1)
	OUT Ports		1.20	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	1
PORT 1	3
PORT 2	4
GND EXT	6
NOT USED	2, 5

#### Functional Diagram

