

Engineering Development Model

Power Splitter/Combiner

ADP-ED7971

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD542

ELECTRICAL SPECIFICATIONS 75Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		100		1000 MHz
Isolation	100-1000MHz		22	dB
Insertion Loss Above 3.0 dB	100-1000MHz		0.5	dB
Phase Unbalance	100-1000MHz		0.35	deg.
Amplitude Unbalance	100-1000MHz		0.05	dB
VSWR	SUM Port		1.76	(:1)
	OUT Ports		1.62	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	1
PORT 1	3
PORT 2	4
GROUND	6
NOT USED	2,5

Functional Diagram



P.O. Box 350188, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4851 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine. Provides ACTUAL Data Instantly From MINN-CIRCUITS At: www.minn-circuits.com

IF/RF MICROWAVE COMPONENTS



REV. X2
ADP-ED7971
12/15/2008
Page 1 of 1