

Engineering Development Model

Power Splitter/Combiner 2 Way-0°

ADP-ED8204/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD636

ELECTRICAL SPECIFICATIONS 75Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		8.54		1067.69	MHz
Isolation	8.54-85.4 MHz		35		dB
	85.4-533.845 MHz		33		dB
	533.845-1067.69 MHz		24		dB
Insertion Loss Above 3.0 dB	8.54-85.4 MHz		0.42		dB
	85.4-533.845 MHz		0.47		dB
	533.845-1067.69 MHz		0.57		dB
Phase Unbalance	8.54-85.4 MHz		0.192		deg.
	85.4-533.845 MHz		1.661		deg.
	533.845-1067.69 MHz		3.287		deg.
Amplitude Unbalance	8.54-85.4 MHz		0.236		dB
	85.4-533.845 MHz		0.354		dB
	533.845-1067.69 MHz		0.584		dB
VSWR	SUM Port		1.11		(:1)
	OUT Ports		1.13		(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	6
PORT 1	4
PORT 2	3
EXTERNAL 2 pF CAPACITOR TO GROUND	2
GROUND	1
NOT USED	5

Functional Diagram



Mini-Circuits®

ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350168, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4951 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINICIRCUITS At: www.minicircuits.com

II/RF MICROWAVE COMPONENTS

minicircuits.com

REV. X2
ADP-ED8204/1
12/15/2008
Page 1 of 1