RF Transformer

0.06 to 400 MHz


Maximum Ratings

Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.5W
DC Current	30mA
Permanent damage may occur if any	of these limits are exceeded


Pin Connections

PRIMARY DOT	3
PRIMARY	1
SECONDARY DOT	4
SECONDARY	6
SECONDARY CT	5
NOT USED	2

Outline Drawing



PCB Land Pattern




Suggested Layout, Tolerance to be within ±.002

Outline Dimensions (inch)

G	F	E	D	C	B	A
.100	.055	. 162	.100	.220	. 310	. 272
2.54	1.40	4.11	2.54	5.59	7.87	6.91
wt grams 0.25			L . 300 7.62	K . 065 1.65	J . 026 0.66	H .030 0.76

Demo Board MCL P/N: TB-430

Config. A



ADT3-6T+



Generic photo used for illustration purposes only

CASE STYLE: CD636

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost el Size Devices/Reel 7" 20, 50, 100, 200

Features

- excellent amplitude unbalance, 0.5 dB typ. in 1 dB bandwidth
- excellent return loss, 20 dB typ. in 1 dB bandwidth
- aqueous washable
- protected under US patent 6,133,525

Applications

- impedance matching
- balanced amplifier

Transformer Electrical Specifications


Ω RATIO (Secondary/Primary)	FREQUENCY INSERTION LOSS*		(INSERTION LOSS*		UNBAI (De	ASE LANCE eg.) /p.	UNBAI (d	ITUDE LANCE B) /p.
		3 dB MHz	2 dB MHz	1 dB MHz	1 dB bandwidth	2 dB bandwidth	1 dB bandwidth	2 dB bandwidth	
3	0.06-400	0.06-400	0.1-290	0.2-250	4	5	0.1	0.2	

^{*} Insertion Loss is referenced to mid-band loss, 0.35 dB typ.

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)		
0.06	0.55	12.87		
0.10	0.38	17.17		
30.00	0.29	33.48		
90.00	0.38	26.75		
190.00	0.50	20.77		
258.00	0.63	17.75		
278.00	0.66	17.18		
312.00	0.81	15.81		
367.00	0.90	14.02		
400.00	1.13	13.03		





- Notes
 A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp