

Frequency Mixer

ALY-ED5505/1

Level 13 (LO Power +13 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CB518

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	3300		6900	MHz
	RF (f _L to f _U)	3300		6900	MHz
	IF	10		1005	MHz
Conversion Loss			6.4		dB
LO-RF Isolation			24		dB
LO-IF Isolation			19		dB

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	1
RF	6
IF	10
GROUND	2, 3, 4, 5, 7, 8, 9