


THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M163111	NEW RELEASE	02/18	DK	YB
OR	R92246	NEW RELEASE	02/18	DK	YB

SUGGESTED MOUNTING CONFIGURATION

FOR PQ2482 CASE STYLE 04DC01 PIN CONNECTION, 50 OHM



NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS R05880 WITH DIELECTRIC THICKNESS. $.015 \pm .0015$ ". COPPER: 1 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm .01$ 3 PL DECIMALS $\pm .005$ ANGLES $\pm 1^\circ$ FRACTIONS $\pm$

DRAWN

DK

19 FEB 18

CHECKED

RM

19 FEB 18

APPROVED

YB

19 FEB 18



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235PL FOR QCH PQ2482
TB-977+ (50 Ω)SIZE
ACODE IDENT
15542

DRAWING NO:

98-PL-526

REV:

OR

FILE: 98-PL-526(OR)

SCALE:

1:1

SHEET:

1 OF 1

ASHEETA1.DWG REV:A DATE:01/12/95

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.