

# Coaxial Bandpass Filter

## BBP-101+

50 $\Omega$

94 to 108 MHz



Generic photo used for illustration purposes only  
CASE STYLE: FF55

## The Big Deal

- Flat group delay over passband
- Narrow bandwidth
- Good VSWR (1.2:1 typical)
- Fast roll-off
- High rejection

## Product Overview

BBP-101+ is a 50 $\Omega$  bandpass filter in a connectorized package. The bandpass filter covers from 94 to 108 MHz, and offers good matching within the passband with high out of band rejection. The filter uses miniature high Q capacitors and wire welded inductors for high reliability. It has repeatable performance across production lots and consistent performance across temperature.

## Key Features

Feature	Advantages
Flat group delay over passband	The model has group delay over passband around 45 ns
Good VSWR, 1.2:1 typical over passband	This provides well matched input and output ports.
High rejection	This enables the filter to attenuate spurious signals and reject harmonics for broad frequency band.
Connectorized package	Connectorized package is easy to interface with other devices and well suited for test setups.

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Bandpass Filter

50Ω 94 to 108 MHz

## BBP-101+



Generic photo used for illustration purposes only

CASE STYLE: FF55

Connectors Model  
BNC BBP-101+

### Features

- Flat group delay over passband
- Good VSWR, 1.2:1 typical in passband
- High rejection, 60 dB typ
- Rugged shielded case
- Connectorized package
- Fast roll-off

### Applications

- Test equipment
- Harmonic rejection
- Transmitters / Receivers
- Military

### Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center frequency	-	-	101	-	MHz
	Insertion Loss	F1-F2	-	2.3	3.5	dB
	VSWR	F1-F2	-	1.2	1.6	:1
Stop Band, Lower	Insertion Loss	DC-F3	50	65	-	dB
		F3-F4	20	29	-	dB
	VSWR	DC-F4	-	20	-	:1
Stop Band, Upper	Insertion Loss	F5-F6	20	28	-	dB
		F6-F7	50	60	-	dB
	VSWR	F7-F8	-	40	-	dB
			-	20	-	:1

### Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.25 W max.

Permanent damage may occur if any of these limits are exceeded.

### Functional Schematic



### Typical Frequency Response







#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
1	88.85	84.83	94.0	51.17
10	71.57	64.16	94.5	49.18
30	65.06	47.20	95.0	47.44
50	65.99	47.41	95.5	45.94
79	31.55	36.76	96.0	44.65
80	29.37	34.02	96.5	43.55
83	22.30	24.16	97.0	42.60
91	3.31	1.65	97.5	41.76
94	2.19	1.19	98.0	41.03
101	1.80	1.05	98.5	40.39
108	1.98	1.12	99.0	39.82
124	20.71	16.97	99.5	39.32
130	27.84	23.53	100.0	38.88
133	30.83	26.35	100.5	38.49
145	40.41	35.58	101.0	38.18
200	70.25	69.12	101.5	37.91
680	93.18	198.49	102.0	37.69
1000	70.76	104.09	106.0	37.67
1500	68.61	51.28	107.0	38.36
2000	58.15	41.32	108.0	39.51



#### Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



Coaxial Connections

PORT - 1	BNC-Male
PORT - 2	BNC-Female

Outline Drawing



Outline Dimensions (  $\frac{\text{inch}}{\text{mm}}$  )

A	B	C	D	E	Wt.
--	<b>0.57</b>	--	<b>2.59</b>	--	grams
--	14.47	--	65.79	--	40

Note: Please refer to case style drawing for details

Notes  
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)