

# Coaxial Bandpass Filter

## BBP-20R5+

50Ω 20 to 21 MHz



Generic photo used for illustration purposes only

CASE STYLE: FF55

|            |           |
|------------|-----------|
| Connectors | Model     |
| BNC        | BBP-20R5+ |

### Features

- Flat group delay over passband
- Good VSWR, 1.3:1 typical in passband
- High rejection (40dB form 40-380 MHz)

### Applications

- Transmitters / Receivers - IF stage
- Harmonic rejection
- Test equipments
- Military

### Electrical Specifications at 25°C


| Parameter        | F#               | Frequency (MHz) | Min.      | Typ. | Max. | Unit |
|------------------|------------------|-----------------|-----------|------|------|------|
| Pass Band        | Center Frequency | -               | -         | 20.5 | -    | MHz  |
|                  | Insertion Loss   | F1-F2           | 20 - 21   | 2.2  | 3.0  | dB   |
|                  | VSWR             | F1-F2           | 20 - 21   | 1.3  | 1.6  | :1   |
| Stop Band, Lower | Insertion Loss   | DC-F3           | DC - 15.8 | 40   | 50   | dB   |
|                  |                  | F3-F4           | 15.8 - 17 | 20   | 27   | dB   |
|                  | VSWR             | DC-F4           | DC - 17   | -    | 20   | :1   |
| Stop Band, Upper | Insertion Loss   | F5-F6           | 27 - 40   | 20   | 28   | dB   |
|                  |                  | F6-F7           | 40 - 380  | 40   | 45   | dB   |
|                  | VSWR             | F5-F7           | 27 - 380  | -    | 20   | :1   |

### Maximum Ratings


|                       |                |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |
| RF Power Input        | 0.5 W max.     |

Permanent damage may occur if any of these limits are exceeded.

### Functional Schematic



### Typical Frequency Response







### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) | Frequency (MHz) | Group Delay (ns) |
|-----------------|---------------------|-----------|-----------------|------------------|
| 1.0             | 98.76               | 3744.00   | 19.5            | 282.22           |
| 10.0            | 81.53               | 1498.50   | 19.6            | 271.33           |
| 15.0            | 62.87               | 174.64    | 19.7            | 262.11           |
| 15.8            | 50.22               | 112.05    | 19.8            | 254.31           |
| 17.0            | 32.36               | 48.32     | 19.9            | 247.41           |
| 17.1            | 30.76               | 44.24     | 20.0            | 241.31           |
| 17.7            | 20.43               | 22.27     | 20.1            | 235.95           |
| 18.0            | 14.68               | 13.12     | 20.2            | 231.18           |
| 18.7            | 3.41                | 1.85      | 20.3            | 226.99           |
| 20.0            | 1.49                | 1.03      | 20.4            | 223.32           |
| 20.5            | 1.40                | 1.03      | 20.5            | 220.13           |
| 21.0            | 1.40                | 1.18      | 20.6            | 217.33           |
| 22.7            | 3.53                | 2.91      | 20.7            | 214.95           |
| 24.0            | 13.84               | 22.15     | 20.8            | 212.81           |
| 25.0            | 20.33               | 48.71     | 20.9            | 210.93           |
| 27.0            | 28.91               | 111.48    | 21.0            | 209.38           |
| 27.5            | 30.49               | 126.54    | 21.1            | 208.18           |
| 40.0            | 47.04               | 320.77    | 21.2            | 207.31           |
| 150.0           | 59.97               | 93.85     | 21.3            | 207.06           |
| 380.0           | 49.47               | 61.09     | 21.5            | 208.37           |



### Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Coaxial Connections

|          |            |
|----------|------------|
| PORT - 1 | BNC-MALE   |
| PORT - 2 | BNC-FEMALE |

## Outline Drawing



## Outline Dimensions ( $\frac{\text{inch}}{\text{mm}}$ )

| A  | B     | C  | D     | E  | Wt.   |
|----|-------|----|-------|----|-------|
| -- | 0.57  | -- | 2.59  | -- | grams |
| -- | 14.47 | -- | 65.79 | -- | 40    |

Note: Please refer to case style drawing for details

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

