

Band Pass Filter

BBPF-EDU0590

Coaxial

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : H16

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Passband (Loss < 5dB)	12		14	MHz
Center Frequency		13		MHz
Stopband Low Band (Loss > 20 dB)	10		11	MHz
Low Band (Loss > 40 dB)	DC		10.	MHz
High Band (Loss > 20 dB)	15.5		19	MHz
High Band (Loss > 40 dB)	19		100	MHz
Passband VSWR		1.4		(:1)
Stopband VSWR		18		(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.4W at 25°C

Functional Schematic

