


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-027258	NEW RELEASE	OCT 25	DDR	VC

138xØ.010 PTH,
PLUGGED WITH EPOXY
& CAPPED WITH Cu



1. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR ROGERS (RO4835 Lo Pro), DIELECTRIC THICKNESS: .0073±.0007. COPPER: 1/2 Oz. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED		INITIALS		DATE	
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±		DRAWN	DDR	08 OCT 25	
		CHECKED	GTP	08 OCT 25	
		APPROVED	RKS	08 OCT 25	



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, JV1210C-8, TB-LDPV-11163+

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-841		REV: OR
FILE: 98-PL-841		SCALE: 9:1	SHEET: 1 OF 1	

ASHEETA1.DWG REV:A DATE:01/12/95

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.