Ceramic

Bandpass Filter

4400 to 5200 MHz 50Ω

BFCN-4800+



Generic photo used for illustration purposes only

CASE STYLE: FV1206

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




Features


- Good VSWR, 1.2:1 typ @ passband
- Small size (0.126 x 0.063 x .037)
- Temperature stable
- LTCC construction

Applications

- · Harmonic rejection
- Telemetry
- Satellite
- Mobile
- · Military and Commercial



Specification Definition




Electrical Specifications^{1,2} at 25°C

Paran	neter	F#	Frequency (MHz)	ency (MHz) Min. Typ.		Max.	Unit
	Center Frequency	_			4800		MHz
Pass Band	Insertion Loss	F1 - F2	4400 - 5200	_	_	2.0	dB
	VSWR	F1 - F2	4400 - 5200	_	_	1.7	:1
Oten Dend Lemm	Insertion Loss	DC - F3	DC - 1800	_	25	_	dB
Stop Band, Lower	VSWR	DC - F3	F1 - F2 4400 - 5200 DC - F3 DC - 1800 DC - F3 DC - 1800	_	30	_	:1
Cton Bond Ilmnor	Insertion Loss	F4 - F5	7500 - 12000	_	25	_	dB
Stop Band, Upper	VSWR F4 - F5		7500 - 12000	_	15	_	:1

- 1. Measured on Mini-Circuits Characterization Test Board TB-270.
 2. This filter is not intended for use as a DC Blocking circuit element. In Application where DC voltage is present at either input or output ports, blocking capacitors are required at the corresponding RF port


Functional Schematic





Maximum Ratings


0 " -	===0.
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to +100°C
RF Power Input*	1.5W at 25°C


*Passband rating, derate linearly to 0.25W at 100°C ambient Permanent damage may occur if any of these limits are exceeded.











Pad Connections

Input	1
Output	3
Ground	2,4

Full Band Performance


Pass Band Performance


Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Insertion Loss (dB)	Group Delay (nsec)
10.00	86.56	349.26	4400.00	0.79	0.30
100.00	75.22	412.74	4500.00	0.72	0.29
1000.00	50.52	206.71	4600.00	0.69	0.29
1800.00	30.99	92.77	4700.00	0.67	0.29
4400.00	0.79	1.32	4800.00	0.67	0.28
5200.00	0.81	1.23	4900.00	0.69	0.28
7500.00	31.68	35.89	5000.00	0.71	0.29
10000.00	27.39	87.13	5100.00	0.75	0.30
12000.00	22.49	58.68	5200.00	0.81	0.30

Pad Connections

Input	1
Output	3
Ground	2,4

Product Marking: BB **Outline Drawing**






Outline Dimensions (inch)

	G	F	E	D	С	В	Α
	.169	.009	.032	.020	.037	.063	.126
	4.29	0.23	0.81	0.51	0.94	1.60	3.20
wt	Р	N	M	L	K	J	Н
grams	.071	.012	.087	.024	.122	.024	.087
.020	1.80	0.30	2.21	0.61	3.10	0.61	2.21

Demo Board MCL P/N: TB-270+ Suggested PCB Layout (PL-137)



NOTES: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH THICKNESS .020" ± .0015".
COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp