

Bandpass Filter

SMT

BFCN-ED13635/6

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : FV1206

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C							
Parameters		F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Pass Band	Center Frequency				1445		MHz
	Insertion Loss	F1-F2	1420-1470			3.0	dB
	VSWR	F1-F2	1420-1470			2.5	:1
Stop Band, Lower	Insertion Loss	DC-F5	300-1000	30			dB
		F5-F3	1000-1190		20		dB
	VSWR	DC-F3	DC-1190		25		:1
Stop Band, Upper	Insertion Loss	F4-F6	2050-2850		25		dB
		F6-F7	2850-3840	30	15		dB
	VSWR	F4-F7	2050-3840		20		:1

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	1.5W max. @ 25°C

*Passband rating, derate linearly to 0.25W at 100°C ambient

PIN CONNECTIONS	
RF IN	1
RF OUT	3
GROUND	2,4

