

PRODUCT CHANGE NOTICE

PCN Form (D4-E000-73)

PCN#17-085

NOTIFICATION DATE: November 13, 2017

MODEL(S) AFFECTED:

QCV-151+
QCV-151-1+
QCV-151-2

EXTENT OF CHANGE:

Change of specification resulting from performance shift.
See attached revised Spec Sheets of QCV-151+.

EFFECT OF CHANGE:

Change FUNCTION (performance)
No change to FORM (appearance) or FIT (dimensions)

REASON FOR CHANGE:

Manufacturing tolerance

EFFECTIVE DATE OF CHANGE:

Immediate

ATTACHMENTS:

n/a

QUESTIONS?

[PLEASE CONTACT US.](#)

2 Way-90° Power Splitter

QCV-151+

50Ω 90 to 150 MHz



CASE STYLE: JV1210C-1

The Big Deal

- High Power handling (10W)
- Low Unbalance, 0.5 dB & 4 deg. typ.
- Industry leading combination of size/bandwidth

Product Overview

Mini-Circuits new 90° Power Splitter, model QCV-151+, offers an industry leading combination of operating bandwidth and size; supporting nearly an octave band in a miniature EIA-1210 form factor. The outstanding phase and amplitude unbalance make this component a versatile building block for use in a variety of systems and sub-system designs.

Key Features

Feature	Advantages
Small Size	Offered in the EIA-1210 package size, the QCV-151+ offers an industry leading combination of size, bandwidth and frequency. The small footprint (3.2mm x 2.0mm) allows for reduced parasitics in systems with improved performance and simplified layout.
Low Phase and Amplitude Unbalance	Supporting 4 deg. and 0.5 dB unbalance make this 90° hybrid applicable for use in higher level integrated components such as image reject mixers, single sideband modulators, phase shifters, variable attenuators, and balance amplifiers.
High Power Handling	Capable of operating up to 10W, the LTCC construction of the QCV-151+ makes this 90° hybrid a robust, rugged product that can be used effectively in either the transmit or receive paths.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MOLStore/terms.jsp



www.minicircuits.com P.O. Box 350186, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Surface Mount

Power Splitter/Combiner

2 Way-90° 50Ω 90 to 150 MHz

QCV-151+



CASE STYLE: JV1210C-1

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	10W* max.



* Derate linearly to 3W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.

Pin Connections

SUM PORT	1
PORT 1 (0°)	4
PORT 2 (+90°)	6
GROUND	2.5
50 OHM TERM EXTERNAL	3

Product Marking: CB

Outline Drawing




Suggested Layout,
Tolerance to be within ±.002

Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.126	.098	.059	.004	.022	.016	.038
3.2	2.5	1.50	0.1	0.56	0.4	1.0
H	J	K	L	M	Wt	
-	-	.177	.024	.059	grams	
-	-	4.5	0.6	1.5	0.03	

Demo Board MCL P/N: TB-610+

Suggested PCB Layout (PL-340)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGER'S RO4330B WITH DIELECTRIC THICKNESS 0.007" ± 0.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. DEMOTES PCB COPPER LAYOUT WITH SMOKE (SOLDER MASK OVER BARE COPPER).
4. DEMOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp

Features

- low insertion loss, 0.4 dB typ.
- high isolation, 20 dB typ.
- ultra small size, 0.12x0.10x.059"
- wrap-around terminal for excellent solderability

Applications

- I/Q modulators
- image reject mixers
- balanced amplifiers
- avionics

+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500, 1000, 2000

Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		90		150	MHz
Insertion Loss (Avg. of coupled outputs above 3 dB)	90-118 118-138 138-150	— — —	0.5 0.6 0.9	0.8 0.95 1.35	dB
Isolation	90-118 118-138 138-150	17 14 11	20 17 15	— — —	dB
Phase Unbalance	90-118 118-138 138-150	— — —	3.0 2.8 4.0	4.0 5.5 10.8	Degree
Amplitude Unbalance	90-118 118-138 138-150	— — —	1.1 0.3 0.9	1.6 0.75 1.7	dB
VSWR (Port S)	90-118 118-138 138-150	— — —	1.2 1.3 1.45	1.4 1.55 1.8	:1
VSWR (Port 1-2)	90-118 118-138 138-150	— — —	1.2 1.3 1.5	1.4 1.6 1.9	:1

Electrical Schematic



7

Mini-Circuits




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. C - TMP
M184532
QCV-151+
ED-13423C/1
AD/CP/AM
171110

Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
90.00	2.92	3.91	0.99	26.73	88.22	1.13	1.13	1.15
95.00	3.05	3.77	0.72	25.92	88.29	1.14	1.14	1.16
100.00	3.17	3.68	0.49	25.10	88.39	1.15	1.15	1.17
105.00	3.27	3.58	0.30	24.27	88.52	1.16	1.16	1.18
110.00	3.36	3.52	0.15	23.42	88.70	1.18	1.17	1.20
115.00	3.43	3.48	0.05	22.56	88.93	1.19	1.19	1.22
120.00	3.49	3.48	0.01	21.66	89.23	1.21	1.20	1.24
125.00	3.53	3.50	0.03	20.73	89.60	1.24	1.23	1.27
130.00	3.55	3.55	0.01	19.77	90.09	1.27	1.26	1.29
135.00	3.55	3.64	0.09	18.77	90.71	1.30	1.29	1.33
140.00	3.54	3.77	0.24	17.76	91.54	1.34	1.33	1.37
145.00	3.51	3.96	0.45	16.73	92.64	1.38	1.37	1.42
150.00	3.48	4.20	0.73	15.68	94.11	1.44	1.43	1.48

¹ Total Loss = Insertion Loss + 3 dB splitter loss.



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MOLStore/terms.jsp

