

24F-24F+

50Ω DC to 50 GHz 2.4 mm-Female to 2.4 mm-Female

THE BIG DEAL

- Ultra-Wideband, DC-50 GHz
- Flat Response
- Low Insertion Loss, 0.14 dB
- Excellent VSWR, 1.03:1



Generic photo used for illustration purposes only

| Model No. | 24F-24F+ | | |
|------------|----------------------|--|--|
| Case Style | DJ2477 | | |
| Connectors | 2.4 mm-F to 2.4 mm-F | | |

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

APPLICATIONS

· Interconnection of RF cable and equipment

PRODUCT OVERVIEW

Mini-Circuits' 24F-24F+ is a coaxial 2.4 mm-F to 2.4 mm-F adapter supporting a wide range of applications from DC to 50 GHz. This model provides excellent VSWR, low insertion loss, and flat response versus frequency. The 24F-24F+ features passivated stainless steel construction and measures only 0.77" (I) x 0.31" (dia.).

KEY FEATURES

| Features | Advantages |
|---|--|
| Wideband, DC to 50 GHz | Wide frequency range provides application flexibility and makes this model ideal for broadband and multi-band use. |
| Excellent VSWR, 1.03:1 | Provides good matching for 50Ω systems and minimizes signal reflections across wide frequency range. |
| Low Insertion Loss, 0.14 dB | Provides excellent signal power transmission from input to output. |
| Passivated stainless steel construction. | Stands up to wear and tear in demanding environments and provides excellent reliability. |
| Very wide operating temperature range, -55 to +100°C | Withstands extreme operating conditions and is suitable for use near high power componentry where heat rise is common. |

PAGE 1 OF 4

24F-24F+

 50Ω DC to 50 GHz 2.4 mm-Female to 2.4 mm-Female

ELECTRICAL SPECIFICATIONS AT 25°C

| Parameter | Condition (GHz) | Min. | Тур. | Max. | Units |
|-----------------|-----------------|------|------|------|-------|
| Frequency Range | _ | DC | _ | 50 | GHz |
| | DC - 5 | _ | 0.04 | 0.4 | |
| | 5 - 10 | _ | 0.08 | 0.4 | |
| Insertion Loss | 10 - 20 | _ | 0.11 | 0.4 | dB |
| | 20 - 40 | _ | 0.14 | 0.4 | |
| | 40 - 50 | _ | 0.18 | 0.4 | |
| | DC - 5 | _ | 1.01 | 1.15 | |
| | 5 - 10 | _ | 1.02 | 1.15 | |
| VSWR | 10 - 20 | _ | 1.02 | 1.15 | :1 |
| | 20 - 40 | _ | 1.02 | 1.15 | |
| | 40 - 50 | _ | 1.03 | 1.15 | |

ABSOLUTE MAXIMUM RATINGS

| Parameter | Ratings | | |
|-----------------------|-----------------|--|--|
| Operating Temperature | -55°C to +100°C | | |
| Storage Temperature | -55°C to +100°C | | |

Permanent damage may occur if any of these limits are exceeded.




 50Ω DC to 50 GHz 2.4 mm-Female to 2.4 mm-Female

COAXIAL CONNECTIONS

| Connector 1 | 2.4 mm-F | | |
|-------------|----------|--|--|
| Connector 2 | 2.4 mm-F | | |

OUTLINE DRAWING



OUTLINE DIMENSIONS (Inches)


| Α | В | С | D | Ε | wt |
|-------|-------|---|-------|---|-------|
| 0.307 | 0.276 | | 0.768 | | grams |
| 7.8 | 7.0 | | 19.5 | | 4.0 |


24F-24F+

50Ω DC to 50 GHz 2.4 mm-Female to 2.4 mm-Female

TYPICAL PERFORMANCE DATA AND CHARTS

| Frequency (GHz) | Insertion Loss (dB) | VSWR (:1) | | |
|--------------------|------------------------|---------------|---------------|--|
| | | 2.4 mm-Female | 2.4 mm-Female | |
| 0.01 | 0.010 | 1.01 | 1.01 | |
| 0.5 | 0.020 | 1.01 | 1.01 | |
| 1.0 | 0.030 | 1.01 | 1.01 | |
| 5.0 | 0.071 | 1.03 | 1.02 | |
| 10.0 | 0.097 | 1.02 | 1.03 | |
| 15.0 | 0.102 | 1.04 | 1.02 | |
| 15.0 | 0.102 | 1.04 | 1.02 | |
| 20.0 | 0.125 | 1.04 | 1.04 | |
| 24.0 | 0.133 | 1.01 | 1.01 | |
| 26.0 | 0.135 | 1.03 | 1.03 | |
| 30.0 | 0.154 | 1.04 | 1.06 | |
| 32.0 | 0.149 | 1.03 | 1.05 | |
| 36.0 | 0.149 | 1.05 | 1.03 | |
| 40.0 | 0.158 | 1.06 | 1.06 | |





NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

