Surface Mount **Bandpass Filter**

BPF-A1600+

 50Ω 1400 to 1800 MHz

Mini-Circuits

Generic photo used for illustration purposes only CASE STYLE: HQ1157

The Big Deal

- Wide bandwidth
- Better rejection
- Miniature shielded package

Product Overview

The BPF-A1600+ is a 50Ω bandpass filter fabricated using SMT technology. This bandpass filter covers from 1400-1800 MHz. This filter is built with high Q capacitors and air-coil inductors for superior performance. This filter is developed for square kilometer array telescope systems for radio astronomy. It has repeatable performance across lots and consistent performance across temperature.

Key Features

Feature	Advantages				
Low insertion loss	Can be used in high performance applications such as radio astronomy.				
Good rejection	This enables the filter to attenuate spurious signals and reject harmonics for broad frequency band.				
Shielded case	Reduced interference with and from the surrounding components.				

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Bandpass Filter

 50Ω 1400 to 1800 MHz

BPF-A1600+



Generic photo used for illustration purposes only CASE STYLE: HQ1157


Features

- · Wide bandwidth
- Better rejection
- · Miniature shielded package


Applications

- Radio telescope applications
- · Public cellular networks (GSM)
- International mobile telecommunication
- Weather instruments / Radar / Satellite

Functional Schematic



Typical Frequency Response



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C


The state of the s								
Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit	
	Center Frequency	_	_	_	1600	_	MHz	
Pass Band	Insertion Loss	F1-F2	1400-1800	_	3.0	4.0	dB	
	VSWR	F1-F2	1400-1800	_	1.5	1.9	:1	
Otan Dand Laws	Insertion Loss	DC-F3	DC-1220	20	30	_	dB	
Stop Band, Lower	VSWR	DC-F3	DC-1220	–	11	_	:1	
Ston Bond Unner	Insertion Loss	F4-F5	1980-3300	20	30	_	dB	
Stop Band, Upper	VSWR	F4-F5	1980-3300	_	5.0	_	:1	


Maximum Ratings				
Operating Temperature	-40°C to 85°C			
Storage Temperature	-55°C to 100°C			
RF Power Input	1 W			


Permanent damage may occur if any of these limits are exceeded.


Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	102.63	1737.18	1400	3.79
750	51.91	31.60	1420	3.35
1220	36.36	12.35	1440	3.09
1280	18.19	10.50	1460	2.93
1315	9.62	6.26	1480	2.81
1340	4.67	2.92	1500	2.69
1370	2.12	1.21	1520	2.60
1400	1.75	1.27	1540	2.54
1500	1.57	1.39	1560	2.51
1600	1.60	1.38	1600	2.53
1700	1.76	1.22	1620	2.57
1800	2.45	1.11	1630	2.60
1845	5.02	1.96	1650	2.65
1875	10.23	3.61	1670	2.70
1930	23.49	7.83	1690	2.76
1980	35.53	11.38	1700	2.80
2200	51.78	20.95	1730	2.98
2760	53.52	29.96	1760	3.30
3010	54.45	32.18	1780	3.64
3300	47.40	34.07	1800	4.11









Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Pad Connections

INPUT	1
OUTPUT	8
GROUND	2,3,4,5,6,7,9,10,11,12,13,14

Demo Board MCL P/N: TB-363+ Suggested PCB Layout (PL-227)




NOTE:

- 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025"±.002". COPPER: 1/2 OZ. EACH SIDE.
 FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER) DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing



Outline Dimensions (inch)

	В	-	D	_		-	
.365	1.360	.35	.100	.180	.140	.100	.100
9.27	34.54	8.89	2.54	4.57	3.56	2.54	2.54
J	K	L	M	N	Р	Q	Wt.
.305	.150	.120	.275	.152	.405	1.400	grams
7.75	3.81	3.05	6.99	3.86	10.29	35.56	4.0

Note: Please refer to case style drawing for details

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

