

Frequency Mixer

ADE-201FLH+

Level 10 (LO Power +10 dBm) 90 to 200 MHz



CASE STYLE: CD636

The Big Deal

- Excellent IP3: +28 dBm
- Low conversion loss, 6.5 dB
- Excellent P1dB compression, +13 dBm at input
- High L-R isolation, 42 dB
- High L-I isolation, 35 dB

Product Overview

Mini-Circuits' ADE-201FLH+ is a surface mount frequency mixer providing high IP3 performance, ideal for minimizing 3rd order intermodulation distortion in multiple carrier environments and other systems where unwanted signals may be present. It also provides high isolation, high P1dB compression point, and low conversion loss. The mixer comes in a compact, six-lead plastic case measuring 0.27 x 0.31 x 0.22", saving space in dense board layouts.

Feature	Advantages
High IP3, +28 dBm	Minimizes third order intermodulation distortion and enables high-dynamic range.
Low conversion loss, 6.5 dB	Enables lower NF front ends, improving system sensitivity.
Excellent P1dB compression, +13 dBm at input	Provides linear performance for a wide range of RF input power levels.
High L-R isolation, (42 dB) and High L-I isolation, (35 dB)	Preserves signal integrity from input to output and reduces undesired signal responses that can interfere with system performance.
Small size (0.27 x 0.31 x 0.22")	Saves board space and accommodates tight layouts.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



High IP3

Frequency Mixer

ADE-201FLH+

Level 10 (LO Power +10 dBm) 90 to 200 MHz



CASE STYLE: CD636


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	20 dBm
LO Power	17 dBm
Permanent damage may occur if any of these limits are exceeded.	


Pin Connections

LO	6
RF	4
IF	3
GROUND	1,2,5

Outline Drawing



PCB Land Pattern




Suggested Layout.
Tolerance to be within ±.002

Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.272	.310	.220	.100	.162	.055	.100
6.91	7.87	5.59	2.54	4.11	1.40	2.54
H	J	K	L			wt
.030	.026	.065	.300			grams
0.76	0.66	1.65	7.62			0.25

Demo Board MCL P/N: TB-02
Suggested PCB Layout (PL-051)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
■ DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- excellent IP3, 28 dBm typ.
- excellent P1dB compression, +13 dBm at input
- good L-R isolation, 42 dB typ.
- good L-I isolation, 35 dB typ.
- aqueous washable
- protected by U.S. patent 6,133,525

Applications

- cellular
- mobil radio
- wireless communication service


Electrical Specifications at 25°C

Parameter	Min.	Typ.	Max.	Unit
Frequency Range, RF	90	—	200	MHz
Frequency Range, LO	154	—	264	MHz
Frequency Range, IF	10	—	150	MHz
Conversion Loss	—	6.5	8.5	dB
LO to RF Isolation	34	42	—	dB
LO to IF Isolation	26	35	—	dB
IP3	—	28	—	dBm
RF Input Power at 1 dB Compression	—	+13	—	dBm

Typical Performance Data








Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)	IP3 (dBm)
RF	LO	LO +10 dBm	LO +10 dBm	LO +10 dBm	LO +10 dBm	LO +10 dBm	LO +10 dBm
90.10	154.10	7.16	52.92	43.11	1.76	5.21	24.83
100.10	164.10	7.05	51.27	41.15	1.79	5.01	27.86
106.10	170.10	6.90	50.27	39.98	1.82	4.85	28.16
110.10	174.10	6.85	49.36	39.23	1.83	4.71	27.73
112.10	176.10	6.75	48.87	38.85	1.83	4.63	27.48
114.10	178.10	6.67	48.46	38.48	1.82	4.57	28.14
116.10	180.10	6.68	48.21	38.10	1.81	4.48	27.28
118.10	182.10	6.67	47.68	37.72	1.82	4.38	27.89
120.10	184.10	6.64	47.26	37.33	1.81	4.27	28.88
130.10	194.10	6.49	45.43	35.69	1.85	3.60	29.90
136.10	200.10	6.51	44.41	34.74	1.84	3.12	31.16
138.10	202.10	6.51	44.13	34.42	1.82	2.95	30.33
140.10	204.10	6.47	43.86	34.11	1.81	2.78	32.97
142.10	206.10	6.49	43.58	33.81	1.81	2.62	30.88
150.10	214.10	6.48	42.71	32.87	1.86	2.02	30.41
160.10	224.10	6.54	42.05	32.36	1.82	1.63	29.49
170.10	234.10	6.61	42.38	32.72	1.71	1.75	29.48
180.10	244.10	6.71	43.43	33.48	1.71	2.13	31.40
190.10	254.10	6.78	44.65	34.31	1.70	2.54	28.13
200.10	264.10	6.87	45.71	35.06	1.58	2.90	27.67

Electrical Schematic



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
M151107
ADE-201FLH+
ED-16303/1
WL/CP/AM
150518
Page 2 of 3



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

