# Surface Mount **Bandpass Filter**

75Ω 950 to 2250 MHz

## The Big Deal

- Wide bandwidth
- Low insertion loss
- Miniature shielded package

## **BPF-AS1600-75+**



Generic photo used for illustration purposes only CASE STYLE: TK2678

### **Product Overview**

The BPF-AS1600-75+ is a 75 $\Omega$  band pass filter fabricated using SMT technology centered at 1600 MHz. The bandpass filter is designed in a very small (0.433" x 0.276" x 0.197") shielded package that covers 1600 MHz ± 650 MHz bandwidth. They use high Q capacitors and inductors for low insertion loss and has consistent performance across temperature & repeatable performance across lots.

## **Key Features**

Feature	Advantages			
Low insertion loss	Can be used in high performance applications like L-band satellite communication systems.			
Small form factor	This filter can be used in dense layout applications.			
Shielded case	Reduced interference with and from the surrounding components.			

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard Terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



# Surface Mount **Bandpass Filter**

75Ω 950 to 2250 MHz

## **BPF-AS1600-75+**



Generic photo used for illustration purposes only CASE STYLE: TK2678


#### **Features**

- · Wide bandwidth
- · Low passband IL
- · Miniature shielded package


#### **Applications**

- · L-Band satellite applications
- Telecommunication & broadband wireless system
- Base station controllers
- Weather instruments / Radar networks

#### **Functional Schematic**



#### **Typical Frequency Response**



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

#### Electrical Specifications at 25°C


Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	_	—	_	1600	_	MHz
Pass Band	Insertion Loss	F1-F2	950-2250		1.0	1.6	dB
	VSWR	F1-F2	950-2250	_	1.6	2.0	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-480	20	30	_	dB
	VSWR	DC-F3	DC-480	_	30	-	:1
Stop Bond Upper	Insertion Loss	F4-F5	3000-3500	16	20	_	dB
Stop Band, Upper	VSWR	F4-F5	3000-3500	—	10		:1


Maximum Ratings					
Operating Temperature	-40°C to 85°C				
Storage Temperature	-55°C to 100°C				
RF Power Input	1 W				


Permanent damage may occur if any of these limits are exceeded.

#### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)	
10	70.96	354.40	950	0.99	
250	57.52	356.60	1000	0.92	
448	30.12	83.21	1050	0.85	
480	26.49	66.98	1100	0.79	
538	20.14	44.08	1150	0.74	
650	8.53	12.06	1200	0.70	
724	3.07	3.69	1250	0.67	
950	0.74	1.41	1300	0.65	
1600	0.53	1.18	1350	0.63	
2250	0.89	1.45	1450	0.60	
2445	3.07	3.25	1450	0.60	
2650	9.81	8.71	1500	0.59	
2700	12.85	9.80	1550	0.58	
2790	20.57	10.75	1600	0.58	
2840	27.14	10.94	1700	0.58	
2860	30.80	11.14	1800	0.58	
3000	29.14	14.13	1900	0.59	
3200	25.64	23.45	2000	0.62	
3400	27.04	27.90	2100	0.68	
3500	27.85	26.90	2250	0.81	







Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard Terms and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

REV.A M174392 BPF-AS1600-75+ EDU3336 URJ 190717 Page 2 of 3


### **Mini-Circuits**


FREQUENCY (MHz)

#### **Pad Connections**

RF IN	1
RF OUT	6
GROUND	3,4,7,8,11,12
NOT CONNECTED	2,5,9,10

#### Demo Board MCL P/N: TB-1072+ Suggested PCB Layout (PL-599)





NOTES:


- TRACE WIDTH IS SHOWN FOR ROGERS(R04350B) WITH DIELECTRIC THICKNESS .030"±.002". COPPER: 1/2 OZ EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
   BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

  - DENOTES PCB COPPER LAYOUT WITH SMOBC

(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

#### **Outline Drawing**



#### Outline Dimensions ( inch )

A <b>.276</b> 7.01		.197	.134	.067	F <b>.047</b> 1.19	.077	.093	.028	.335
L <b>.049</b> 1.24	M . <b>364</b> 9.25	.303	.201	.063	R <b>.030</b> 0.76	.177			Wt. grams 0.6

Note: Please refer to case style drawing for details

Notes
 A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specification advector of the specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the evolve rights and emedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

