Bandpass Filter

BPF-B199+

 50Ω 194 to 204 MHz

The Big Deal

- Narrow band filter (BW of 5%)
- Excellent VSWR (1.2:1 typical)
- Wide stopband rejection till 2GHz (70 dB typical)
- Fast roll-off



CASE STYLE: HZ1198

Product Overview

The BPF-B199+ is a narrow-band bandpass filter in a shielded package (size of 0.472" x 0.826" x .22") fabricated using SMT technology. Covering 199 MHz \pm 5 MHz band width, these units offer good matching within the passband and high rejection. This unit uses a miniature high Q capacitors and wire welded inductors for high reliability. In addition it has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages
Narrow bandwidth filter (fractional bandwidth of 5%)	Provides sharp rejection which rejects adjacent channel.
Excellent VSWR, 1.2:1 typical in passband	The model has very good return loss for a narrow bandwidth which provides good matching when used with other devices.
More than 50dB rejection up to 2000MHz	This enables the filter to attenuate spurious signals and reject harmonics for broad band of frequency.
Shielded case	Reduced interference with the surrounding components.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuit standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

Bandpass Filter

194 to 204 MHz 50Q

BPF-B199+



CASE STYLE: HZ1198


Features

- Excellent VSWR, 1.2:1 typical in passband
- High rejection, 70 dB typical
- Sharp insertion loss roll-off
- · Shielded case
- · Aqueous washable


Applications

- · Harmonic rejection
- Transmitters / receivers
- Radio communications

Functional Schematic



Typical Frequency Response



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C


Parai	meter	F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	_	_	_	199	_	MHz
Pass Band	Insertion Loss	F1-F2	194-204	_	4.2	5	dB
	VSWR	F1-F2	194-204	_	1.2	1.5	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-179	20	31	_	dB
	VSWR	DC-F3	DC-179	_	24	_	:1
Stop Band, Upper	Insertion Loss	F4-F5	221-2000	20	30	_	dB
Stop Band, Upper	VSWR	F4-F5	221-2000	_	16	_	:1


Maximum Ratings						
Operating Temperature	-40°C to 85°C					
Storage Temperature	-55°C to 100°C					
RF Power Input	0.25W max.					


Permanent damage may occur if any of these limits are exceeded


Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)	
1.0	91.17	91.43	194.0	55.90	
50.0	73.13	51.10	194.5	55.29	
100.0	72.40	62.05	195.0	54.50	
164.0	53.90	64.35	195.5	53.60	
179.0	32.48	27.16	196.0	52.67	
186.0	17.49	9.38	196.5	51.78	
189.0	10.16	4.09	197.0	50.93	
194.0	4.22	1.24	197.5	50.19	
199.0	3.55	1.10	198.0	49.54	
204.0	3.86	1.09	198.5	49.02	
208.0	5.90	1.71	199.0	48.67	
212.0	13.43	5.36	199.5	48.40	
221.0	30.59	17.93	200.0	48.25	
239.0	50.71	41.37	200.5	48.23	
500.0	75.12	173.72	201.0	48.34	
1000.0	76.18	133.63	201.5	48.57	
1300.0	78.02	102.19	202.0	48.92	
1500.0	74.83	86.86	202.5	49.40	
1700.0	55.64	82.73	203.5	50.67	
2000.0	78.44	75.53	204.0	51.37	









A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Pad Connections


INPUT	1
OUTPUT	2
GROUND	3,4,5,6

Demo Board MCL P/N: TB-400+ Suggested PCB Layout (PL-247)




NOTES:


- 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025"±.002". COPPER: 1/2 OZ. EACH SIDE.
 FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing





Suggested Layout, Tolerance to be within ±.002

Outline Dimensions (inch)

.472 11.99	.826 20.98	.220 5.59	.551 14.00	.118 3.00	.047	G .078 1.98	.076 1.93	.142	.543 13.79	.078 1.98	M .236 5.99
N .079 2.01	.138 3.51	Q .162 4.11	.098 2.49	T .096 2.44	.217 5.51	.067	.157 3.99	.866 22.00	.512		wt grams 6.0

- Notes
 A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp