

Frequency Mixer

ADE-ED12872/7

Level 7 (LO Power + 7 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD637

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	10		325	MHz
	RF (f _L to f _U)	10		325	MHz
	IF	10		200	MHz
Conversion Loss	mid band		4.9		dB
	Total Range		5.3		dB
LO-RF Isolation	Low Range		62		dB
	Mid Range		40		dB
	Upper Range		40		dB
LO-IF Isolation	Low Range		58		dB
	Mid Range		45		dB
	Upper Range		40		dB
Input IP3			+10.53		dBm
1 dB Compression			+1		dBm

Note: Low Range = [f_L to 10f_L]
mid band = [2f_L to f_U/2]

Mid Range = [10f_L to f_U/2]

Upper Range = [f_U/2 to f_U]

MAXIMUM RATINGS	
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
LO	6
RF	3
IF	2
GROUND	1,4,5

Electrical Schematic

